

4

3

2




1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			L	REV PER 0G3A-0256-04	08APR04	JR TM



STAMPING DETAIL

- 1 FOR9.14 [.360] MAX WIRE INSULATION DIA.
- 2 SUPERSEDED BY 53234-1
- 3 MATERIAL: BODY; COPPER PER ASTM B152 INSULATION; PVC COLOR: TRANSLUCENT
- 4 FINISH: BODY; TIN PLATE PER ASTM B545

AMP WIRE RANGE	Listed	LR7189 Certified
22-12 AWG STRANDED	22-12 AWG STRANDED	22-12 AWG STRANDED



100	LOOSE PC,BOX	8-53234-1	2
250	LOOSE PIECE	53234-1	
QTY	DESCRIPTION	PART NO	


AMP INCORPORATED
CUSTOMER SERVICE SYSTEMSFOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY


1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.MAX RECOMMENDED OPERATING
TEMPERATURE:
105°C MAXVOLTAGE RATING:
600V MAX (BUILDING WIRING)
1000V MAX (FIXTURES & SIGNS)CIRCULAR MIL AREA:
1.65-5.78mm² [3248-11400]
STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± -
1 PLC ± -
2 PLC ± 0.20 [.008]
3 PLC ± -
4 PLC ± -
ANGLES ± -
FINISHDWN
G KRUPER 1/15/93CHK
R HERSEY 1/15/93APVD
M ELLIS 1/15/93

PRODUCT SPEC

UL 486 C

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics Corporation
Harrisburg, PA 17105NAME
SPLICE, CLOSED END,
WIRE SIZE, 22-12 AWGSIZE CAGE CODE DRAWING NO RESTRICTED TO
A3 00779 C-53234

SCALE 2:1 SHEET 1 OF 1 REV L