

Series KU
Base Mount Double Row Terminal Blocks



SPECIFICATIONS

Rating: 60A, 600V*
Center Spacing: .625" (15.88 mm)
Number of poles: 2 - 12
Wire Size: AWG #6 CU max.
Screw Size: #10-32 brass nickel plated
Torque Rating: 20 in/lb max.
Distance Between Barriers: .437" (11.09 mm)
Mounting: Base mount. For 35mm DIN rail mountable, consult factory.
Material: Molded base: Black, UL rated 94V-0 thermoplastic. Terminal plating: Nickel over brass. Screws: Nickel plated brass.
Operating Temperature: 105°C max.
Approvals: UL E62622; CSA LR15364; CE Pending





Table with 4 columns: No. of Poles, KU A, KU B, KUX only A. Rows for pole counts 2 through 12.

Dimensions in inches. To convert to millimeters, multiply by 25.4.
*60A rating achieved with #6 copper wire crimped to ring terminal



Part Numbering System

Series: KU, KUX, KUSC, KURL, KUXSC, KUXRL
Poles: 2 to 12
Screw Options: 00, W, P, B
Covers: WC
Marking Strip: MT, NU, NUV, PT

Accessories

MTMU## Molded Marking Tape Matte Finish
NUM## Molded Marking Tape
JU12 Jumper 12 Circuits
NUE End Piece for NUC
NUC## Cover