

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0757570441

Status:


Active

Overview:

MX150™ Unshrouded Header

Description:

MX150 Single Row Header, Vertical, 4 Circuits, 1.25µm Nickel (Ni) Overall, 1.50µm Minimum Select Matte Tin (Sn) Plating Overall, 11.20mm Mating Pin Length, 3.05mm PC Tail Length



Series image - Reference only

- Documents:
- 3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-75757-000-001 (PDF)

Packaging Specification PK-36518-342 (PDF)

Packaging Specification PK-75757-007 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Headers
Series	75757
Application	Power, Wire-to-Board
Overview	MX150™ Unshrouded Header
Product Name	MX150
UPC	883906195182
Physical	
Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.009/g
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.05mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Tube
Pitch - Mating Interface	3.50mm
Pitch - Termination Interface	3.50mm
Plating min - Mating	1.524µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	17.0A
Voltage - Maximum	500V DC

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2020)4578-DC (25

June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

75757 Series

Mates With

33471 Single Row MX150 Receptacles

Solder Process Data

Lead-freeProcess Capability

WAVE

Material Info

Reference - Drawing Numbers

Packaging Specification

PK-36518-342, PK-75757-007

Product Specification

PS-75757-000-001

Sales Drawing

AS-75900-104, SD-75757-010-001

This document was generated on 07/17/2020

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION