



GBU401 - GBU407

Single Phase 4.0 AMPS. Glass Passivated
Bridge Rectifiers


GBU

Features

- ✧ UL Recognized File # E-96005
- ✧ Ideal for printed circuit board
- ✧ Reliable low cost construction
- ✧ Plastic material has Underwriters Laboratory Flammability Classification 94V-0
- ✧ High case dielectric strength of 1500VRMS
- ✧ Surge overload rating to 150 amperes peak
- ✧ High temperature soldering guaranteed: 260°C / 10 seconds / .375", (9.5mm) lead lengths at 5 lbs., (2.3kg) tension

Mechanical Data

- ✧ Case: Molded plastic body
- ✧ Terminals: Leads solderable per MIL-STD-750, Method 2026
- ✧ Weight: 0.3 ounce, 8.0 grams
- ✧ Mounting torque: 5 in. lbs. Max.



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	GBU 401	GBU 402	GBU 403	GBU 404	GBU 405	GBU 406	GBU 407	Units
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current @ T _C = 100 °C	I _(AV)	4.0							A
Peak Forward Surge Current, 8.3 ms Single Half Sne-wave Superimposed on Rated Load (JEDEC method)	I _{FSM}	150							A
Maximum Instantaneous Forward Voltage @ 2.0A @ 4.0A	V _F	1.0 1.1							V
Maximum DC Reverse Current @ T _A =25 °C at Rated DC Blocking Voltage @ T _A =125 °C	I _R	5.0 500							uA uA
Typical Junction Capacitance (Note 3)	C _j	100				45			pF
Typical Thermal Resistance (Note 1) (Note 2)	R _{θJA} R _{θJC}	20 4.0							°C/W
Operating Temperature Range	T _J	-55 to +150							°C
Storage Temperature Range	T _{STG}	-55 to + 150							°C

- Notes:
1. Mounted on P.C.B. with 0.5" x 0.5" (12mm x 12mm) Copper Pads and 0.375" 9.5mm) Lead Length.
 2. Mounted on Al. Plate of 2" x 3" x 0.25" Al-Plate Heatsink.
 3. Measured at 1.0MHZ and Applied Reverse Voltage of 4.0 Volts.

RATINGS AND CHARACTERISTIC CURVES (GBU401 THRU GBU407)

FIG.1-MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2- TYPICAL REVERSE CHARACTERISTICS PER BRIDGE ELEMENT




FIG.3- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT PER BRIDGE ELEMENT




FIG.4- TYPICAL JUNCTION CAPACITANCE




FIG.5- TYPICAL FORWARD CHARACTERISTICS PER BRIDGE ELEMENT

