

1	2	3	4
Empfohlener Ausschnitt fuer Rastbefestigung (Gegensueber Bestueckungsseite) recommended cut-out for snap-in fixing (edge opposite to snap-in direction)	Wanddicke wall thickness	Ausschnittlaenge length of cut-out	Ausschnittbreite width of cut-out
	0.75 bis / to 1.25 1.25 bis / to 3	30 ^{+0.1} 30.2 ^{+0.1}	22 ^{+0.2} 22 ^{+0.2}

Die in unseren Unterlagen angegebene IP Schutzklasse bezieht sich auf die Betaetigungsseite des Schalters, wenn dieser in das Kundengerat eingebaut ist. Die Abdichtung zwischen Schalter und Kundengerat kann ueber die umlaufende Dichtlippe der Betaetigungskappe erfolgen. Die Montage in das Kundengerat und die Pruefung auf Dichtheit an dieser Stelle erfolgen kundenseitig. Schalter mit beschaedigten Betaetigungskappen muessen sofort ausgetauscht werden.

The IP-protection class mentioned in our documents refers to the actuating side of the switch when mounted into the customer appliance. The sealing between switch and customer appliance is realizable through the surrounding sealing lip of the actuating cap. The mounting into the customer appliance and the testing of the tightness have to be effected by the customer. Switches with damaged actuating caps have to be replaced immediately.

Flachstecker/plug-in
DIN 46244-A6.3x0.8

**Aufschrift
Marking**

193..
10181/250 ~ 5E4
20141/250 ~ T105/55
5/120A 250V ~
05
16A 125-250V AC
3/4 HP 125V AC
1 HP 250V AC
R188

1 — 2

Ausschalter 2-polig
Fuer Geraete der Klasse II geeignet

DPST
suitable for appliances of class II

Herstellort/-jahr/-woche nach DIN EN 60062
code of manufacture: place/year/week acc. to DIN EN 60062

GERAETESCHALTER
appliance switch

fuer Form und Lage FOR SHAPE AND LOC. fuer Winkel FOR ANGLE ± 2	⊙ =	Allgemeintoleranzen UNTOLERANCED DIMENSIONS				Pause COPY 0 10 20 30mm	Blatt SHEET 01	TYP K	Zeichn./DRAWING NO. 19323114	Index a	
		PROJEKTION	Abmasse und Nennmassbereiche Angaben in mm	Loenge LENGTH	Radien RADI		Original Din A4	Massstab SCALE 1:1 30mm	GERAETESCHALTER appliance switch		
		ALL DIMENSIONS ARE IN MILLIMETRES	0-6 ± 0.15 ± 0.2	>6-15 ± 0.2 ± 0.3	>15-30 ± 0.25 ± 0.5						
		>30-70 ± 0.4 >70-120 ± 0.6 >120-200 ± 1.0	± 10%								
						CAD: NX v4.0		MARQUARDT			
						gez./DRAWN BY 05.05.08 hhe					
						gepr./CHECKED BY					
Ausg. ISSUE	Aenderung REVISION	gez. DRAWN BY	Ausg. ISSUE	Aenderung REVISION	gez. DRAWN BY	Ersatz fuer/REPLACEMENT OF Zg.gl.Nr.v.14.06.2004					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Marquardt:](#)

[1932.3114](#)