



1. THIS DIMENSION REPRESENTS THE LENGTH FROM THE CONNECTOR CENTERLINE TO THE CABLE EXIT POINT (NOT SHRINK TUBE)
2. ELECTRICAL PERFORMANCE SHOWN FOR SSMT CONNECTOR AND CABLE ONLY.
FOR MMCX CONNECTOR REFER TO DESIGN OBJECTIVES 108–2084.
FOR CABLE ASSEMBLY DATA CONSULT FACTORY.
3. ASSEMBLE MMCX CONNECTOR TO CABLE PER INSTRUCTION SHEET 408–8627
4. OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



 OBSOLETE	300±5	1408483-3
	200±5	1408483-2
	100±3	1408483-1
	LENGTH A	PART NUMBER

<u>ELECTRICAL</u>		FREQUENCY NOMINAL IMPEDENCE VOLTAGE RATING VSWR (MATED CONNECTORS ONLY) INSULATION RESISTANCE DIELECTRIC WITHSTANDING VOLTAGE		DC — 6 GHz 50 OHMS 250 VOLTS (VRMS MAX) @ SEA LEVEL 1.20:1 MAX @ 2 GHz 1.40:1 MAX @ 6 GHz 1,000 MEGOHMS MIN @ 250VDC 500 VOLTS (VRMS MIN) @ SEA LEVEL	
<u>MECHANICAL</u>		CONNECTOR DURABILITY		100 MATING CYCLES	
<u>ENVIRONMENTAL</u>		TEMPERATURE RATING		-40°C(-40°F) TO +125°C(257°F)	
PRODUCT SPEC					
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK SCHRUM 04MAY2006 CHK KE WEIDNER 04MAY2006 APVD KE WEIDNER 04MAY2006		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.13 4 PLC ± - ANGLES ± 1°		NAME SSMT RIGHT ANGLE JACK TO MMCX STRAIGHT PLUG INTERSERIES CABLE ASSEMBLY	
		PRODUCT SPEC — APPLICATION SPEC —		SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 00779 C=1408483 —	
MATERIAL —		FINISH —		WEIGHT —	
CUSTOMER DRAWING				SCALE	NTS 1 OF 1
				SHEET	REV
					B1