








20 CIRCUIT RIGHT ANGLE
HEADER ASSEMBLY SHOWN


DATECODE, SEE NOTE 6



SECTION Z-Z





HARNESS ASSEMBLY
SEE SALES DRAWING
SD-30700-120.



NOTES:

1. MATERIAL: HOUSING: SPS, GLASS FILLED, COLOR: SEE CHART.
TERMINAL: COPPER ALLOY.
PIN ALIGNMENT PLATE: MYLAR, COLOR: NATURAL (WHITE).
2. FINISHES: TERMINAL: TIN (Sn) OVERALL,
THICKNESS = 1.5 MICROMETER MINIMUM;
NICKEL (Ni) UNDERPLATE OVERALL.
3. PRODUCT SPECIFICATION: PS-30700-0001
4. PACKAGING SPECIFICATION : TUBE: PK-30907-227, TRAY: PK-30907-260
5. MATES WITH: SERIES 30700, SEE SALES DRAWING SD-30700-120.
6. DATECODE DESCRIPTION:
 - 1ST DIGIT: MACHINE ID# (ALWAYS WILL BE '2')
 - 2ND THROUGH 4TH DIGIT: DAY# OF THE CALENDAR YEAR (EXAMPLE: FEB. 3RD = '034')
 - 5TH DIGIT: LAST DIGIT OF THE CALENDAR YEAR (EXAMPLE: 1999 = '9')
 - 6TH THROUGH 7TH DIGIT: HOUR OF THE DAY.
7. RECOMMENDED OPTIONAL SCREW: M2 x 0.89, 6mm IN LENGTH, PAN COLLAR HEAD, 6 LOBE.
TORQUE: 7 NEWTON CENTIMETERS

BELOW VIEWS APPLY TO
30700-5067/8/9 PART NUMBERS



SEE ECN# UAU2001-0258 EC NO: UAU2014-1769 DRWN: JFISCHERO 2014/05/19 CHKD: APPR: RBAUMAN 2014/05/28 B3	QUALITY SYMBOLS - 0 C - 0	DESCRIPTION REV	GENERAL TOLERANCES (UNLESS SPECIFIED)	mm		INCH		SCALE 2:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION	REVISE ON CAD ONLY							
				4 PLACES ± ---		± ---		DIMENSION STYLE MM ONLY			TITLE 6-20 CIRCUIT RIGHT ANGLE HEADER ASSEMBLY MOLEX INCORPORATED							
				3 PLACES ± ---		± ---		DRAWN BY RCARLSON						DATE 01/03/20				
				2 PLACES ± 0.13		± ---		CHECKED BY CKRISHNA						DATE 01/03/27				
				1 PLACE ± 0.25		± ---		APPROVED BY LGEIB						DATE 01/03/28		MATERIAL NO. ENTER-PART		DOCUMENT NO. SD-30700-520
				ANGULAR ± 1 °														
				DRAFT WHERE APPLICABLE														
				MUST REMAIN WITHIN DIMENSIONS														

