




NOTES:


1. LED includes integrated diode for reverse voltage protection.
2. LED includes integrated resistor for current limiting.

Operating Temperature Range	-30°C to +85°C
Storage Temperature Range	-40°C to +100°C

TYPICAL ELECTRICAL & OPTICAL OPERATING CHARACTERISTICS

(Ta = 25 degree C)

PART NUMBER	EMITTING COLOR	AMPERAGE mA	VOLTAGE Vdc	LUMENS	μW/cm ²	DOMINANT WAVELENGTH	VIEWING ANGLE DEGREES
LE-0503-03R	RED	15mA	12.0	0.70	—	630nm	20
LE-0503-03Y	YELLOW	15mA	12.0	0.70	—	595nm	20
LE-0503-03G	GREEN	15mA	12.0	2.00	—	525nm	20
LE-0503-03B	BLUE	15mA	12.0	0.70	—	470nm	20
LE-0503-03W	9000°K WHITE	15mA	12.0	2.50	—	x = 0.30 y = 0.29	20
LE-0503-03UV	ULTRA VIOLET	15mA	12.0	—	235	405	20

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION TITLE T-3 1/4 WEDGE BASE LED						
E	ADD 9000° WHITE	6/16/10	DRAWN BY L. WENGSTROM APPV'D BY L.R. DATE 6/16/10 - CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SIZE	FSCM NO.	DRAWING NO.						
D	CHANGE MOL TO 27.5 ± 1.0	1/22/09			A	55335	LE-0503-03						
C	CHANGE CHARTS	8/25/08											
B	ADDITIONAL ELECT INFO & CHNG DIMS	8/11/08											
A	CHNG. LUMENS & ADD NOTES 1 & 2	9/14/06											
ENGR RELEASE & CANCEL PL-0503-03-1 TO -6			3/3/05	SCALE		RELEASED DATE		7/03/06	REVISION DATE	6/16/10	REV. NO.	E	SHEET 1 OF 1
REV. NO.	DESCRIPTION/ECO NUMBER		APPV'D DATE			NONE							