


Twin Diode Module TDM150



Dim.	Inches		Millimeters		Notes
	Min.	Max.	Min.	Max.	
A	---	3.630	---	92.20	
B	0.700	0.800	17.78	20.32	
C	---	0.625	---	15.87	
E	0.120	0.130	3.05	3.30	
F	0.490	0.510	12.45	12.95	
G	1.375	BSC	34.92	BSC	
H	---	0.050	---	1.27	
N	1/4-20	UNC	---	---	
Q	.280	.310	6.86	7.11	Dia.
R	3.150	BSC	80.01	BSC	
U	0.600	---	15.24	---	
V	0.330	0.350	8.38	8.89	
W	0.170	0.190	4.32	4.82	Dia.
Y	1.815	BSC	46.10	BSC	

Microsemi Catalog Number	Working Peak Reverse Voltage	Repetitive Peak Reverse Voltage
TDM15002*	200V	200V
TDM15004*	400V	400V
TDM15006*	600V	600V
TDM15008*	800V	800V
TDM15010*	1000V	1000V
TDM15012*	1200V	1200V
TDM15014*	1400V	1400V
TDM15016*	1600V	1600V

*Add Suffix A for Common Anode, D for Doubler

- Compact Package
- Glass Passivated Die
- 2 x 150 Amp Current Rating
- Simplifies Circuit Assembly
- High Surge Capacity

Electrical Characteristics

Average forward current per pkg	$I_F(AV)$ 300 Amps	$T_C = 120^\circ C$, half sine, $R_{\theta JC} = 0.15^\circ C/W$
Average forward current per leg	$I_F(AV)$ 150 Amps	$T_C = 120^\circ C$, half sine, $R_{\theta JC} = 0.30^\circ C/W$
Maximum surge current per leg	I_{FSM} 2500 Amps	8.3 ms, half sine, $T_J = 175^\circ C$
Max I^2t for fusing	I^2t 26000 A^2s	
Max peak forward voltage per leg	V_{FM} 1.1 volts	$I_{FM} = 200A$; $T_J = 25^\circ C^*$
Max peak reverse current per leg	I_{RM} 5 mA	$V_{RRM}, T_J = 150^\circ C$
Typical reverse current per leg	I_{RM} 50 μA	$V_{RRM}, T_J = 25^\circ C$

*Pulse test: Pulse width 300 usec, Duty cycle 2%

Thermal and Mechanical Characteristics

Storage temp range	T_{STG}	$-55^\circ C$ to $175^\circ C$
Operating junction temp range	T_J	$-55^\circ C$ to $175^\circ C$
Max thermal resistance per leg	$R_{\theta JC}$	$0.3^\circ C/W$ Junction to case
Typical thermal resistance per leg (greased)	$R_{\theta CS}$	$0.08^\circ C/W$ Case to sink
Terminal Torque		40-50 inch pounds
Mounting Base Torque (outside holes)		30-40 inch pounds
Mounting Base Torque (center hole)		8-10 inch pounds
center hole must be torqued first		
Weight		2.82 ounces (80 grams) typical

TDM150

Figure 1
Typical Forward Characteristics – Per Leg




Figure 3
Forward Current Derating – Per Leg




Figure 4
Maximum Forward Power Dissipation – Per Leg




Figure 2
Typical Reverse Characteristics – Per Leg




Figure 5
Transient Thermal Impedance – Per Leg

