






RECOMMENDED P.C.B. LAYOUT


SCALE 3:1



CIRCUIT: SPST

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
X.XX=±0.25
2. GENERAL TOLERANCE: X.XX=±0.4
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATINGS: 12VDC, 50mA
5. OPERATING FORCE: 100±50gf
6. TRAVEL: 0.25±0.1mm
7. CONTACT RESISTANCE: 100 mΩ Max.
8. DIELECTRIC STRENGTH: 250V RMS min.
9. INSULATION RESISTANCE: 100 Mega Ω min.
10. ELECTRICAL LIFE: 100,000 CYCLES min.
11. DESIGNATE MAJOR FEATURE:



10. ELECTRICAL LIFE: 100,000 CYCLES min.			
▲ 11. DESIGNATE MAJOR FEATURE:			
A	11621	RELEASED FOR PRODUCTION	8/20/01 CJB
REV.	ECN No.	DESCRIPTION	DATE CHKD
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
TITLE		SCALE	
TL1105F F100 Q		4:1	
DATE		DR	
--		--	
DWG		REV	
P010027		A	