





1. ALL DIMENSIONS SHOWN ARE MAXIMUM UNLESS OTHERWISE SPECIFIED.
2. CABLE ASSEMBLY SHALL BE WIRED PER WIRING DIAGRAM.
3. MATERIAL:
- CONNECTOR HOUSINGS- POLYCARBONATE, UL 94V-0 RATED, WHITE.
- STRAIN RELIEFS- CARBON STEEL WITH NICKEL PLATING 5.08µm [.000200] MINIMUM THICK.
- CONTACTS- COPPER ALLOY WITH SILVER PLATED STRIP 3.81µm [.000150] MINIMUM THICK.
4. DIMENSION A SHALL BE MEASURED WITH CONDUIT IN THE RELAXED POSITION.
5. DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.
6. MANUFACTURING LOCATION, DATE CODE, PART NUMBER AND LENGTH SHALL BE INK STAMPED WHERE INDICATED.
7. APPLICATION: AMPINNERGY - MODULAR POWER DISTRIBUTION SYSTEM, A MANUFACTURED WIRING SYSTEM.
8. USE GROUND WIRE INSPECTION WINDOW TO VERIFY BONDING AND GROUNDING CONDUCTOR.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN J MCNEAL 11AUG2005 CHK F LINCOLN 11AUG2005 APVD F LINCOLN 11AUG2005		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		CABLE ASSEMBLY, POWER ENTRY, 5 WIRE	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ±	± ± ± ± ±	PRODUCT SPEC APPLICATION SPEC		-	
MATERIAL - 		ANGLES FINISH - 		WEIGHT -		SIZE A100779	CAGE CODE C=555858
CUSTOMER DRAWING				SCALE 1:1		SHEET 1 OF 1	REV U