




PRODUCT NUMBER
SEE TABLE



mat'l. code				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family LATCH-N-LOK			
ltr ecn nodr date				tolerances unless otherwise specified						title			
H	ELX-N-008457	ZK	11/28/11	angles	linear	XXX±.01/0.XX±0.3		INCH/MM		2X10 LNL LOW PROFILE RT. ANGLE HEADER ASSEMBLY			
C	V10987	TFG	3/1/01			0°±2°	XXX±.005/0.XX±0.13						
D	M05-0062	ERE	4/01/05			dr	M. CORNMANN	10/29/90	scale 1:1				
E	M06-0285	AGS	7/28/06	engr	D. HORCHLER	10/29/90			dwg no		sheet 1 of 2	size	
F	M06-0365	AGS	9/20/06	chr	D. HORCHLER	10/29/90			79610		A3		
G	M09-0048	MHT	3/12/09	appd	D. HORCHLER	10/29/90			type Product Customer Drawing				
sheet revision				H	H								
index sheet				1	2								


79610-XXXLF

LEAD FREE OPTION ⑥⑦

	COLOR ④	
1	70343 LT GRAY	OBS
2	80166 OFF WHITE	
3	70634 DK GRAY	OBS
4	701 BLACK	
5	70511 SLATE GRAY	OBS
7	70455 SILVER GRAY	
8	80189 PEARL WHITE	OBS
9	70419 PEBBLE GRAY	

	PLATING ③
0	30u" MIN OVER 50u"MIN Ni
3	30u" MIN OVER 50u"MIN Ni
5	50u" MIN OVER 50u"MIN Ni

	PIN LENGTH
	DIM L
0	.200/5.08
1	.130/3.30



NOTES:

- HEADER SHROUD
MAT'L: HIGH TEMPERATURE THERMOPLASTIC,
UL-94V-0 RATED.
- GROUND CONTACT
MAT'L: COPPER ALLOY
PLATING: 100-160u"/2.54-4.06u TIN.
- SIGNAL CONTACT
MAT'L: COPPER ALLOY
PLATING OPTION: PERFORMANCE PLATING WILL BE EITHER GOLD OR GXT
ON CONTACT AREA OR TAIL, OPTIONALLY (78-295u") TIN ON TAIL.
- NUMBERS SHOWN ARE FOR G.E. LEXAN
AND ARE FOR REFERENCE ONLY.
- THIS ASSEMBLY UL APPROVED PER FILE E66906 VOL. 1, SEC. 84
AND CSA APPROVED PER MASTER FILE LR 46923. PACKAGING
- ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.
- THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- PRODUCT SPEC: GS-12-003

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection INCH/MM		product family LATCH-N-LOK	
ltr ecn nodr date		tolerances unless otherwise specified		title		dwg no		sheet 2 of 2 size	
H		angles	linea	2X10 LNL LOW PROFILE RT. ANGLE HEADER ASSEMBLY		79610		A3	
		0°±2°		scale 1:1					
		dr	M. CORNMANN	10/29/90					
		engr	D. HORCHLER	10/29/90					
		chr	D. HORCHLER	10/29/90					
		appd	D. HORCHLER	10/29/90					
sheet index		revision sheet							