

Type:	2032 ws, 2032 sw	
Description:	Rewirable plug with protective contact, center-straight-entry, DIN 49441-R1 CEE7/IV	
APSA-EDV-Code:	A2032 ws: A2032.0000.01.000 A2032 sw: A2032.0000.02.000	
EAN-Code:	A2032 ws: 4000993120323 A2032 sw: 4000993220320	

Rated voltage, Rated current, IP-code

250V_{AC}, 16A, IP20

Number of poles

2P + PE (R1 earthing contact system)

Kind of construction

DIN 49441-R1, CEE7/IV

Terminals

nominal cross-sectional areas of conductors: 0,75 up to 2,5mm²
Terminals: screw-type

Cord


max. diameter: 8,5mm, limited by the protective sleeve aperture

Stripping

2P: X=40mm, PE: X=45mm, conductor for clamp: Y=7mm

Protective sleeve

unaffected, natural Ø6.5
extendable to Ø8.5
removable



Cord anchorage

Material: polypropylene (PP)

Enclosure

Material: polypropylene (PP)

Contacts

2P-pins: brass, nickel-plated
PE protective contact: brass, natural, not plated

Screws plating

2P + PE	nickel-plated
Fixing screws	zinc-plated

Colors

2029 ws:	Enclosure
2029 sw	white
	black

Marks Licence

VDE by VDE Testing and Certification Institute according to DIN VDE 0620-1 (VDE 0620-1):2005-04

EC Declaration of Conformity


73/23/EEC including amendments

ROHS Declaration of Conformity

2002/95/EC


doc_info

file:	APSA_DATASHEET_2032_B_1.pdf
date of issue:	2006-05-04
valid from:	2006-05-04



A-A

Screw head:



Cord anchorage:



B-Typ

Dateiname des Zeichnungsobjektes: APSA_2032_BG_PLUG_M_TÜ_00_B								
				Datum	Name	Rewirable plug with protective contact center-straight-entry DIN49441-R1 CEE7/IV Type: 2032		
				Bear.	05.02.2008			pu
				Gepr.				
				Norm				
						APSA_DATASHEET_2032_B.pdf 2/2		
Zust.	Änderung	Datum	Nam	(Urspr.)	(Ers.f.:	(Ers.d.:		