

TE Internal #: F27532-000

Standard Labels, Industrial Label, Die-Cut Label Style, Permanent

Acrylic Adhesive, UL Listed No, Label Width 16.5 mm [.64 in]

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > CP CLEAR POLYESTER LABELS



Label Type: Industrial Label

Label Style: Die-Cut

Label Adhesive Type: Permanent Acrylic Adhesive

UL Listed: No

Label Width: 16.5 mm [.64 in]

[All CP CLEAR POLYESTER LABELS \(18\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Label Color	Clear
-------------	-------

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	5
Recommended Printer Ribbon	See Printer Ribbon Matrix
Label Style	Die-Cut
Label Width	16.5 mm [.64 in]
Label Height	10.2 mm [.4 in]
Label Material	Polyester
Label Thickness	72 Micron

Industry Standards

UL Listed	No
-----------	----

Packaging Features

Packaging Quantity	10000
--------------------	-------

Packaging Method

Roll

Other

Label Adhesive Type

Permanent Acrylic Adhesive

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021
(211)Candidate List Declared Against: JAN 2021
(211)

Does not contain REACH SVHC

Halogen Content

Not Yet Reviewed for halogen content

Solder Process Capability

Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-2186500-1
T3212-PRINTERTE Part # 1-2186502-1
T3224-PRINTERTE Part # 1-2186501-1
T3212-SWARE-PRINTER

Customers Also Bought



Documents

Product Drawings

[CP-165102-10-X](#)

English

Datasheets & Catalog Pages

[TTDS-083, Rev2](#)

English

[IDENTIFICATION SELECTION GUIDE](#)

English