

# EP1345ETTS-30.086M



## ELECTRICAL SPECIFICATIONS


|                                   |                                                                                                                                                                                                                                  |
|-----------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nominal Frequency                 | 30.086MHz                                                                                                                                                                                                                        |
| Frequency Tolerance/Stability     | ±50ppm Maximum (Inclusive of all conditions: Calibration Tolerance at 25°C, Frequency Stability over the Operating Temperature Range, Supply Voltage Change, Output Load Change, First Year Aging at 25°C, Shock, and Vibration) |
| Aging at 25°C                     | ±5ppm/year Maximum                                                                                                                                                                                                               |
| Operating Temperature Range       | -40°C to +85°C                                                                                                                                                                                                                   |
| Supply Voltage                    | 3.3Vdc ±10%                                                                                                                                                                                                                      |
| Input Current                     | 28mA Maximum (Unloaded)                                                                                                                                                                                                          |
| Output Voltage Logic High (Voh)   | Vdd-0.4Vdc Minimum (IOH = -8mA)                                                                                                                                                                                                  |
| Output Voltage Logic Low (Vol)    | 0.4Vdc Maximum (IOL = +8mA)                                                                                                                                                                                                      |
| Rise/Fall Time                    | 4nSec Maximum (Measured at 20% to 80% of waveform)                                                                                                                                                                               |
| Duty Cycle                        | 50 ±10(%) (Measured at 50% of waveform)                                                                                                                                                                                          |
| Load Drive Capability             | 30pF Maximum                                                                                                                                                                                                                     |
| Output Logic Type                 | CMOS                                                                                                                                                                                                                             |
| Pin 1 Connection                  | Tri-State (Disabled Output: High Impedance)                                                                                                                                                                                      |
| Pin 1 Input Voltage (Vih and Vil) | 70% of Vdd Minimum to enable output, 20% of Vdd Maximum to disable output, No Connect to enable output.                                                                                                                          |
| Disable Current                   | 16mA Maximum (Pin 1 = Ground)                                                                                                                                                                                                    |
| Standby Current                   | 20µA Maximum (Pin 1 = Ground)                                                                                                                                                                                                    |
| Peak to Peak Jitter (tPK)         | 100pSec Maximum, 60pSec Typical                                                                                                                                                                                                  |
| RMS Period Jitter (tRMS)          | 13pSec Maximum, 10pSec Typical                                                                                                                                                                                                   |
| Start Up Time                     | 10mSec Maximum                                                                                                                                                                                                                   |
| Storage Temperature Range         | -55°C to +125°C                                                                                                                                                                                                                  |

## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

|                              |                                       |
|------------------------------|---------------------------------------|
| Fine Leak Test               | MIL-STD-883, Method 1014, Condition A |
| Gross Leak Test              | MIL-STD-883, Method 1014, Condition C |
| Lead Integrity               | MIL-STD-883, Method 2004              |
| Mechanical Shock             | MIL-STD-202, Method 213, Condition C  |
| Resistance to Soldering Heat | MIL-STD-202, Method 210               |
| Resistance to Solvents       | MIL-STD-202, Method 215               |
| Solderability                | MIL-STD-883, Method 2003              |
| Temperature Cycling          | MIL-STD-883, Method 1010              |
| Vibration                    | MIL-STD-883, Method 2007, Condition A |


EP1345ETTS-30.086M 


MECHANICAL DIMENSIONS (all dimensions in millimeters)



| PIN | CONNECTION                 |
|-----|----------------------------|
| 1   | Tri-State (High Impedance) |
| 7   | Ground/Case Ground         |
| 8   | Output                     |
| 14  | Supply Voltage             |

| LINE | MARKING                                                                                     |
|------|---------------------------------------------------------------------------------------------|
| 1    | ECLIPTEK                                                                                    |
| 2    | EP13TS<br>EP13=Product Series                                                               |
| 3    | 30.086M                                                                                     |
| 4    | XXYYZZ<br>XX=Ecliptek Manufacturing Code<br>Y=Last Digit of the Year<br>ZZ=Week of the Year |

**OUTPUT WAVEFORM & TIMING DIAGRAM**


**EP1345ETTS-30.086M** **Test Circuit for CMOS Output**

Note 1: An external 0.1  $\mu\text{F}$  low frequency tantalum bypass capacitor in parallel with a 0.01  $\mu\text{F}$  high frequency ceramic bypass capacitor close to the package ground and  $V_{DD}$  pin is required.

Note 2: A low capacitance (<12pF), 10X attenuation factor, high impedance (>10Mohms), and high bandwidth (>300MHz) passive probe is recommended.

Note 3: Capacitance value  $C_L$  includes sum of all probe and fixture capacitance.

## Recommended Solder Reflow Methods



### High Temperature Solder Bath (Wave Solder) Time (t)

|                                            |                                                                                                                                          |
|--------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Ts MAX to Tl (Ramp-up Rate)</b>         | 3°C/Second Maximum                                                                                                                       |
| <b>Preheat</b>                             |                                                                                                                                          |
| - Temperature Minimum (Ts MIN)             | 150°C                                                                                                                                    |
| - Temperature Typical (Ts TYP)             | 175°C                                                                                                                                    |
| - Temperature Maximum (Ts MAX)             | 200°C                                                                                                                                    |
| - Time (ts MIN)                            | 60 - 180 Seconds                                                                                                                         |
| <b>Ramp-up Rate (Tl to Tp)</b>             | 3°C/Second Maximum                                                                                                                       |
| <b>Time Maintained Above:</b>              |                                                                                                                                          |
| - Temperature (Tl)                         | 217°C                                                                                                                                    |
| - Time (tL)                                | 60 - 150 Seconds                                                                                                                         |
| <b>Peak Temperature (Tp)</b>               | 260°C Maximum for 10 Seconds Maximum                                                                                                     |
| <b>Target Peak Temperature (Tp Target)</b> | 250°C +0/-5°C                                                                                                                            |
| <b>Time within 5°C of actual peak (tp)</b> | 20 - 40 Seconds                                                                                                                          |
| <b>Ramp-down Rate</b>                      | 6°C/Second Maximum                                                                                                                       |
| <b>Time 25°C to Peak Temperature (t)</b>   | 8 Minutes Maximum                                                                                                                        |
| <b>Moisture Sensitivity Level</b>          | Level 1                                                                                                                                  |
| <b>Additional Notes</b>                    | Temperatures shown are applied to back of PCB board and device leads only. Do not use this method for product with the Gull Wing option. |

## Recommended Solder Reflow Methods



### Low Temperature Infrared/Convection 185°C

|                                            |                                                                                                               |
|--------------------------------------------|---------------------------------------------------------------------------------------------------------------|
| <b>Ts MAX to Tl (Ramp-up Rate)</b>         | 5°C/Second Maximum                                                                                            |
| <b>Preheat</b>                             |                                                                                                               |
| - Temperature Minimum (Ts MIN)             | N/A                                                                                                           |
| - Temperature Typical (Ts TYP)             | 150°C                                                                                                         |
| - Temperature Maximum (Ts MAX)             | N/A                                                                                                           |
| - Time (ts MIN)                            | 60 - 120 Seconds                                                                                              |
| <b>Ramp-up Rate (Tl to Tp)</b>             | 5°C/Second Maximum                                                                                            |
| <b>Time Maintained Above:</b>              |                                                                                                               |
| - Temperature (Tl)                         | 150°C                                                                                                         |
| - Time (tL)                                | 200 Seconds Maximum                                                                                           |
| <b>Peak Temperature (Tp)</b>               | 185°C Maximum                                                                                                 |
| <b>Target Peak Temperature (Tp Target)</b> | 185°C Maximum 2 Times                                                                                         |
| <b>Time within 5°C of actual peak (tp)</b> | 10 Seconds Maximum 2 Times                                                                                    |
| <b>Ramp-down Rate</b>                      | 5°C/Second Maximum                                                                                            |
| <b>Time 25°C to Peak Temperature (t)</b>   | N/A                                                                                                           |
| <b>Moisture Sensitivity Level</b>          | Level 1                                                                                                       |
| <b>Additional Notes</b>                    | Temperatures shown are applied to body of device. Use this method only for product with the Gull Wing option. |

## Recommended Solder Reflow Methods



### Low Temperature Solder Bath (Wave Solder) Time (t)

|                                            |                                                                                                                                          |
|--------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Ts MAX to Tl (Ramp-up Rate)</b>         | 5°C/Second Maximum                                                                                                                       |
| <b>Preheat</b>                             |                                                                                                                                          |
| - Temperature Minimum (Ts MIN)             | N/A                                                                                                                                      |
| - Temperature Typical (Ts TYP)             | 150°C                                                                                                                                    |
| - Temperature Maximum (Ts MAX)             | N/A                                                                                                                                      |
| - Time (ts MIN)                            | 30 - 60 Seconds                                                                                                                          |
| <b>Ramp-up Rate (Tl to Tp)</b>             | 5°C/Second Maximum                                                                                                                       |
| <b>Time Maintained Above:</b>              |                                                                                                                                          |
| - Temperature (Tl)                         | 150°C                                                                                                                                    |
| - Time (tL)                                | 200 Seconds Maximum                                                                                                                      |
| <b>Peak Temperature (Tp)</b>               | 245°C Maximum                                                                                                                            |
| <b>Target Peak Temperature (Tp Target)</b> | 245°C Maximum 1 Time / 235°C Maximum 2 Times                                                                                             |
| <b>Time within 5°C of actual peak (tp)</b> | 5 Seconds Maximum 1 Time / 15 Seconds Maximum 2 Times                                                                                    |
| <b>Ramp-down Rate</b>                      | 5°C/Second Maximum                                                                                                                       |
| <b>Time 25°C to Peak Temperature (t)</b>   | N/A                                                                                                                                      |
| <b>Moisture Sensitivity Level</b>          | Level 1                                                                                                                                  |
| <b>Additional Notes</b>                    | Temperatures shown are applied to back of PCB board and device leads only. Do not use this method for product with the Gull Wing option. |

### Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum. (Temperatures listed are applied to device leads only. This method can be utilized with both Gull Wing and Non-Gull Wing devices.)

### High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum. (Temperatures listed are applied to device leads only. This method can be utilized with both Gull Wing and Non-Gull Wing devices.)