

# Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



83007 Hook-up/Lead - UL AWM Style 1213

For more Information  
please call

1-800-Belden1



## Description:

Stranded silver-coated copper conductor insulation with extruded TFE Teflon.

## Physical Characteristics (Overall)

### Conductor

AWG:

| # Conductors | AWG | Stranding | Conductor Material         |
|--------------|-----|-----------|----------------------------|
| 1            | 20  | 19x32     | SPC - Silver Plated Copper |

### Insulation

Insulation Material:

| Insulation Material       | Wall Thickness (mm) |
|---------------------------|---------------------|
| TFE - Tetrafluoroethylene | 0.254               |

### Overall Insulation

### Overall Cabling

Overall Nominal Diameter: 1.473 mm

## Applicable Specifications and Agency Compliance (Overall)

### Applicable Standards & Environmental Programs

|                                       |                                      |
|---------------------------------------|--------------------------------------|
| UL AWM Style:                         | 1213                                 |
| UL Rating:                            | 105°C                                |
| EU CE Mark:                           | Yes                                  |
| EU Directive 2000/53/EC (ELV):        | Yes                                  |
| EU Directive 2002/95/EC (RoHS):       | Yes                                  |
| EU RoHS Compliance Date (mm/dd/yyyy): | 04/01/2005                           |
| EU Directive 2002/96/EC (WEEE):       | Yes                                  |
| EU Directive 2003/11/EC (BFR):        | Yes                                  |
| CA Prop 65 (CJ for Wire & Cable):     | Yes                                  |
| MII Order #39 (China RoHS):           | Yes                                  |
| Military Specification:               | MIL-W-16878/4 (Except For Stranding) |
| MIL Spec Rating:                      | 600 V, 200°C                         |

### Flame Test

UL Flame Test: VW-1

### Plenum/Non-Plenum

Plenum (Y/N): No

## Related Documents:

No related documents are available for this product

## Put Ups and Colors:

| Item #       | Putup | Ship Weight | Color | Notes | Item Desc       |
|--------------|-------|-------------|-------|-------|-----------------|
| 83007 001100 | 30 MT | 0.181 KG    | BROWN |       | #20 STR TFE BRN |

## 83007 Hook-up/Lead - UL AWM Style 1213

|               |        |          |             |     |                   |
|---------------|--------|----------|-------------|-----|-------------------|
| 83007 0011000 | 305 MT | 2.722 KG | BROWN       | S W | #20 STR TFE BRN   |
| 83007 002100  | 30 MT  | 0.181 KG | RED         |     | #20 STR TFE RED   |
| 83007 0021000 | 305 MT | 2.722 KG | RED         | S W | #20 STR TFE RED   |
| 83007 002500  | 152 MT | 1.361 KG | RED         | S W | #20 STR TFE RED   |
| 83007 003100  | 30 MT  | 0.181 KG | ORANGE      |     | #20 STR TFE ORG   |
| 83007 0031000 | 305 MT | 2.722 KG | ORANGE      | S W | #20 STR TFE ORG   |
| 83007 004100  | 30 MT  | 0.181 KG | YELLOW      |     | #20 STR TFE YEL   |
| 83007 0041000 | 305 MT | 2.722 KG | YELLOW      | S W | #20 STR TFE YEL   |
| 83007 005100  | 30 MT  | 0.181 KG | GREEN, DARK |     | #20 STR TFE GRNDK |
| 83007 0051000 | 305 MT | 2.722 KG | GREEN, DARK | S W | #20 STR TFE GRNDK |
| 83007 006100  | 30 MT  | 0.181 KG | BLUE, LIGHT |     | #20 STR TFE BLULT |
| 83007 0061000 | 305 MT | 2.722 KG | BLUE, LIGHT | S W | #20 STR TFE BLULT |
| 83007 006500  | 152 MT | 1.361 KG | BLUE, LIGHT | S W | #20 STR TFE BLULT |
| 83007 007100  | 30 MT  | 0.181 KG | VIOLET      |     | #20 STR TFE VIO   |
| 83007 0071000 | 305 MT | 2.722 KG | VIOLET      | S W | #20 STR TFE VIO   |
| 83007 008100  | 30 MT  | 0.181 KG | GRAY        |     | #20 STR TFE GRY   |
| 83007 0081000 | 305 MT | 2.722 KG | GRAY        | S W | #20 STR TFE GRY   |
| 83007 009100  | 30 MT  | 0.181 KG | WHITE       |     | #20 STR TFE WHT   |
| 83007 0091000 | 305 MT | 2.722 KG | WHITE       | S W | #20 STR TFE WHT   |
| 83007 009500  | 152 MT | 1.361 KG | WHITE       | S W | #20 STR TFE WHT   |
| 83007 010100  | 30 MT  | 0.181 KG | BLACK       |     | #20 STR TFE BLK   |
| 83007 0101000 | 305 MT | 2.722 KG | BLACK       | S W | #20 STR TFE BLK   |
| 83007 010500  | 152 MT | 1.361 KG | BLACK       | S W | #20 STR TFE BLK   |

**Notes:**

S = STRIPING ADDERS FOR TYPES E AND EE: 123 STRIPES. MINIMUM ORDER 10  
W = MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 75'

Revision Number: 1    Revision Date: 05-14-2007

© 2011 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.