

Part Number: KCDA56-103

YELLOW


### Features

- 0.56 INCH DIGIT HEIGHT.
- LOW CURRENT OPERATION.
- EXCELLENT CHARACTER APPEARANCE.
- I.C. COMPATIBLE.
- MECHANICALLY RUGGED.
- GRAY FACE, WHITE SEGMENT.
- PACKAGE: 200PCS/ REEL.
- MOISTURE SENSITIVITY LEVEL : LEVEL 4.
- RoHS COMPLIANT

### Description

The Yellow source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Yellow Light Emitting Diode.

### Package Dimensions & Internal Circuit Diagram



#### Notes:

1. All dimensions are in millimeters (inches), Tolerance is  $\pm 0.25$  (0.01") unless otherwise noted.
2. Specifications are subject to change without notice.
3. The gap between the reflector and PCB shall not exceed 0.25mm.

## Selection Guide

| Part No.   | Dice               | Lens Type      | Iv (ucd) [1]<br>@ 10mA |      | Description                     |
|------------|--------------------|----------------|------------------------|------|---------------------------------|
|            |                    |                | Min.                   | Typ. |                                 |
| KCDA56-103 | YELLOW (GaAsP/GaP) | WHITE DIFFUSED | 1200                   | 5000 | Common Anode, Rt. Hand Decimal. |

Note:

1. Luminous Intensity / Luminous Flux: +/-15%.

## Electrical / Optical Characteristics at TA=25°C

| Symbol                | Parameter                | Device | Typ. | Max. | Units | Test Conditions |
|-----------------------|--------------------------|--------|------|------|-------|-----------------|
| $\lambda_{peak}$      | Peak Wavelength          | Yellow | 590  |      | nm    | IF=20mA         |
| $\lambda_D$ [1]       | Dominant Wavelength      | Yellow | 588  |      | nm    | IF=20mA         |
| $\Delta\lambda_{1/2}$ | Spectral Line Half-width | Yellow | 35   |      | nm    | IF=20mA         |
| C                     | Capacitance              | Yellow | 20   |      | pF    | VF=0V;f=1MHz    |
| VF [2]                | Forward Voltage          | Yellow | 2.1  | 2.5  | V     | IF=20mA         |
| IR                    | Reverse Current          | Yellow |      | 10   | uA    | VR = 5V         |

Notes:

1. Wavelength: +/-1nm.


2. Forward Voltage: +/-0.1V.

## Absolute Maximum Ratings at TA=25°C

| Parameter                       | Yellow         | Units |
|---------------------------------|----------------|-------|
| Power dissipation               | 75             | mW    |
| DC Forward Current              | 30             | mA    |
| Peak Forward Current [1]        | 140            | mA    |
| Reverse Voltage                 | 5              | V     |
| Operating / Storage Temperature | -40°C To +85°C |       |





Note:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.




Yellow

KCDA56-103



## KCDA56-103


Reflow Soldering Profile For Lead-free SMT Process.



### NOTES:

1. We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.
2. Don't cause stress to the epoxy resin while it is exposed to high temperature.
3. Number of reflow process shall be 2 times or less.

## Recommended Soldering Pattern (Units : mm; Tolerance: ±0.15)



## Tape Specifications (Units : mm)

