





LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	DWN
			A2	REVISED PER ECR-08-005025	03MAR08	DML

D

C

B

A




1. SPECIFICATIONS
- LEAD WIRE : #14-#10 AWG (2.0-5.6mm²) (4,000-11,000 CMA)
2 WIRES MAX
- MAGNET WIRE: #20-#11 AWG (0.81-2.30mm²) (1,000-9,000 CMA)
8 WIRES MAX
- TOTAL WIRE: 4,000-40,000 CMA
CRIMP HEIGHT: (TOTAL CMA + 39,000) / 516,000

2. CARRIER STRIPS (PHANTOM LINES) TO SCRAP DURING
INSERTION.

- 3 FINISH: PRE-TIN PLATE OVER COPPER UNDERPLATE.

SERRATION DETAIL
SCALE 40X



-		-		-	
3		111-000-001		1601953-1	
FINISH		REFERENCE PART NUMBER		TYCO PART NUMBER	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 18JUL2002		Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: INCHES		CHK G JACONO 18JUL2002		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD G JACONO 18JUL2002		POWER SPLICE	
0 PLC ± -		PRODUCT SPEC		SIZE	
1 PLC ± -		APPLICATION SPEC		CAGE CODE	
2 PLC ± .01[0.13]		114-13093		DRAWING NO	
3 PLC ± .005[0.026]		WEIGHT		RESTRICTED TO	
4 PLC ± -		CUSTOMER DRAWING		A2 00779	
ANGLES ± 3°		SCALE 1:1		SHEET 1 of 1	
MATERIAL BRASS, HALF HARD		FINISH		REV A2	