






AMP
WIRE RANGE

22-16 AWG
SOLID OR STRANDED

- 1 STAMP AMP 22-18 APPROX AS SHOWN
22-16 TERMINALS ARE STAMPED 22-18 IN ACCORDANCE
WITH MILITARY SPECIFICATION SAE AS7928 COMMERCIAL
WIRE RANGE IS 22-16.
- 2 WIRE BARREL COLOR CODED ORANGE TO DENOTE
NICKEL MATERIAL
- 3 GOLD PLATE 0.00127[.000050] MIN EXT THK PER ASTM B488
TYPE1, CODE C OVER NICKEL FLASH PER SAE AMS QQ-N-290
OVER WOODS NICKEL FLASH PER ASTM B558
- 4 NOTE DELETED

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: SEE TABLE
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: NOT APPLICABLE
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	WIRE CROSS SECTIONAL AREA RANGE: 0.26-1.65mm ² [509-3,260] CIR MILS SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

2	----	649°C [1200°F]	5000	ON TAPE	2-321884-2
2	3	260°C [500°F]	1000	LOOSE PIECE	321884-1
2	----	649°C [1200°F]	1000	LOOSE PIECE	321884
	FINISH	MAX OPERATING TEMP	QUANTITY	PACKAGE TYPE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-15-93	 TE Connectivity					
DIMENSIONS: mm [INCHES]		CHK DA PATTERSON 4-15-93						
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD DE MILLER 4-15-93	NAME TERMINAL, RING TONGUE, HIGH TEMPERATURE, STRATO-THERM					
		PRODUCT SPEC —						
		MATERIAL NICKEL PER ASTM B-162 ANNEALED	FINISH SEE TABLE	APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO C-321884	RESTRICTED TO —
				WEIGHT —				
CUSTOMER DRAWING			SCALE 10:1	SHEET 1 of 1	REV D3			