



This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



09 pos.
Drawing for sub-assembly
L171370



09 pos.
Drawing for side
Plastic shell

Customer drawing

Shell size	Commercial Part Number	Dimension						
		Amax	B	Cmax	Dmax	Emax	Fmax	Gmax
E	L171370	31.5	32.8	16.8	39.6	41.6	6.4	4.6
A	L171371	39.8	38.1	16.8	47.9	46.9	9.5	5.6
B	L171372	53.6	38.1	16.8	61.8	47.0	11.4	7.6
C	L171373	70.0	40.5	16.8	83.1	54.2	16.5	9.1



REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1		Release new drawing	12/09/09	IP

D-SUB TECHNICAL DATA

Material and finish:

Shell: Thermoplastic, UL94-V0 color black

Screws: Steel, nickel plated, indication of thread
Should be matched with the plastic shell

Cable clamp: Steel, nickel plated
cable clamp with self-tapping screws

CLIMATIC : Temperature range -30 °C up to 90°C

MARKING : Amphenol-...(Series No.)

Commercial reference

Manufacturing date

PRODUCT CODE

RoHS Compliance

L 17 137 XX


X: None: standard 3#screw
H=4mm
L: Longer 3#screw(H=8mm)

See shell size

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL		DATE
U.S.	METRIC	DRAWN	Christine	12/09/09
.X +/-	0.50	CHECKED	lik.wang	12/09/09
.XX +/-	0.30	CHECKED		
.XXX +/-	0.20			
FRACTIONS +/-	5'			
ANGLES +/-				
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE : drawing\Draw\CL17137X		
REMOVE SHARP EDGES		ANGLE OF PROJECTION		
DIMENSIONS				
U.S.	INCHES			
METRIC	MM			

Amphenol			
TITLE			
Hood, 17 Series			
SIZE	DRAWING NO.	REV.	
A4	C L17 137XX	1	
SCALE	NONE	SHEET 1 OF 2	

This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



15/25/37 pos.
Drawing for sub-assembly
L171371/L171372/L171373

15/25/37 pos.
Drawing for side
Plastic shell

Customer drawing

Shell size	Commercial Part Number	Dimension						
		Amax	B	Cmax	Dmax	Emax	Fmax	Gmax
E	L171370	31.5	32.8	16.8	39.6	41.6	6.4	4.6
A	L171371	39.8	38.1	16.8	47.9	46.9	9.5	5.6
B	L171372	53.6	38.1	16.8	61.8	47.0	11.4	7.6
C	L171373	70.0	40.5	16.8	83.1	54.2	16.5	9.1



REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
1		Release new drawing	12/09/09	IP

D-SUB TECHNICAL DATA

Material and finish:
Shell: Thermoplastic, UL94-V0 color black
Screws: Steel, nickel plated, indication of thread
Should be matched with the plastic shell
Cable clamp: Steel, nickel plated
cable clamp with self-tapping screws
CLIMATIC : Temperature range -30 °C up to 90°C
MARKING : Amphenol-...(Series No.)
Commercial reference
Manufacturing date

PRODUCT CODE

L 17 137 X X

RoHS Compliance

X: None: standard 3#screw
H=4mm
L: Longer 3#screw(H=8mm)

See shell size

UNLESS OTHERWISE SPECIFIED TOLERANCES		APPROVAL		DATE	Amphenol			
U.S.		DRAWN	Christine	12/09/09	TITLE			
METRIC		CHECKED	Wk.wang	12/09/09				
.X	+/-				Hood, 17 Series			
.XX	+/-							
.XXX	+/-				SIZE DRAWING NO.			
FRACTIONS	+/-							
ANGLES	+/-				C L17 137XX			
FOR MATERIALS AND FINISHES SEE NOTES		DRAWING FILE :		drawing\Sub\CL17137X	SCALE NONE			
REMOVE SHARP EDGES		ANGLE OF PROJECTION						
DIMENSIONS					SHEET 2 OF 2			
U.S.	INCHES							
METRIC	MM							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Amphenol:](#)

[L171372](#) [L171373](#) [L171374](#) [L171371](#)