


RED INDICATES ORIGINAL


DASH NO	CABLES ACCOMMODATED	A DIM	B FLATS	C HEX	ASSEMBLE PER
-1	RG-58				
-U1	ESSEX 621-715				
-2	RG-59				
-U2					
-2A	BELDEN 8279				
-U2A					
-2B	W.E.CO. 730A				
-U2B					
-3					
-U3	RG-223	.906	.437	.437	TAI-101
-3A					
-U3A	RG-55				
-4	RG-122				
-U4	BELDEN 8218				
-5	RG-174				
-U5	RG-187				
-5A					
-U5A	RG-196				
-5B	HEWLETT-PACKARD 8120-1107				
-U5B					
-6	BELDEN 9231	.963	.500	.500	TAI-119
-U6					
-6E	RG-5				
-U6E	RG-6				
-21	RG-303				
-U21					
-22	RG-180				
-U22					
-34	BELDEN 8228	.906	.437	.437	TAI-101
-U34					
-36	275-3991 MICRODOT				
-U36	616-569 AMPEX				
-37					
-U37	610 RAYCHEM				
-41	RG-304				
-U41	BELDEN 9248/9284/9383				
-44	BRAND-REX B749				
-U44	GORE C06C032				
-51	88281 BELDEN	.963	.500	.500	TAI-119
-U51					
-52	89120 BELDEN				
-U52					
-53	89555 BELDEN	.906	.437	.437	TAI-101
-U53					
-63	734A.AT&T				
-U63					

FIG 1
- 1 SHOWN



INCH	MM
.005	0.13
.030	0.76
.096	2.44
.125	3.18
.437	11.10
.500	12.70
.562	14.27
.906	23.01
.963	24.46
1.846	46.89

FIG 2
- 1 SHOWN



△ IF BEND RELIEF SPRING REQUIRED, ADD SUFFIX "BR" TO MODEL NO. (SEE FIG 2) (NOT AVAILABLE WITH CABLE GROUPS -6, -U6, -6E, -U6E, -51, -U51, -52, -U52, -63 & -U63)

- MALE COAXIAL PUSH-ON PLUG BOTH 50 & 75 OHM VERSION (BNC STYLE)
- DASH NO DENOTES CABLE GROUP EXCEPT "U" PREFIX DENOTES 75 OHM VERSION
- FINISH: TFS-1A (NICKEL)
- ALL DIM ARE IN INCHES

DISK #	DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS, INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.	REV	EO	DESCRIPTION	REVISIONS	1-0390	SH 1
C 5		6	8594	ADDED -63 CABLE GROUP-DWG NO WAS 1000-0390 & REDRAWN	DWN	APPROVED	DATE

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL UNLESS SPECIFIED .XX ± .XXX ± .XXXX ± ANGLES	TROMPETER ELECTRONICS, INC.	PL123/UPL123	
DWN	DJK 9/15/89	MATERIAL	CODE IDENT
CHK	11/1 10/21/81	14949	DRAWING NO.
ENGR	10/31/89	1-0390	REV
APPR	11/3/89	SCALE 2/1	DATE 7/6/76
12-06	NEXT ASSY		SHEET 1 OF 2