5 and 6-Wire Receptacles, Front Mount, 1/2-14 NPT Threads

TURCK works Industrial Automation

- NEMA 1, 3, 4, 6P
- IEC IP68 Protection

Housing Style	Female Part Number	Male Part Number	Features	Pinout	
FK .. 14.5/NPT  **Typical panel cutout is 22.5 mm.**	FK 4.5-*/14.5/NPT	FS 4.5-*/14.5/NPT	5x22 AWG, 105°C, 250 V, 4 A, mates with 5-pin cordsets	1. BN 2. WH 3. BU 4. BK 5. GY	Female  Male 
	FK 4.6-*/14.5/NPT	FS 4.6-*/14.5/NPT	6x22 AWG, 105°C, 250 V, 4 A, mates with 6-pin cordsets	1. BN 2. WH 3. BU 4. BK 5. GY 6. PK	Female  Male 
FS ..14.5/NPT  **Typical panel cutout is 22.5 mm.**	FK 6-*/14.5/NPT	FS 6-*/14.5/NPT	6x24 AWG, 105°C, 60 VAC/75 VDC, 2 A, mates with 6-pin cordsets		Female  Male 

* Length in meters. Standard lead length is 0.5 Meters. Consult factory for other lengths.
Standard housing material is nickel plated brass "FS.."; "FSV.." indicates stainless steel.
To specify PVC jacketed cable, add "/S717" to the end of the part number.