

T30R1STNLM5

High Temp Cable Tie, 5.8" Long, 30lb Tensile Strength, PA46, Brown, 1000/plain pkg

Article Number: 111-03027

Part Number: T30R1STNLM5

Type: T30R



→Find a Distributor

→Order Samples


→Get Technical Drawings

| Share

→Base Data

Part No.	T30R1STNLM5
Type	T30R
Color	Brown (BN)
Features	• Cable ties made of PA46 material provide a greater resistance to high heat exposures than PA66 heat stabilized material. • Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

→Product Dimensions



Min. Tensile Strength	30.0lbs / 135.0N
Length (L)	5.8" / 148.0mm
Width (W) (imperial)	0.14"
Width (W)	3.6mm
Min. Ø Bundle	0.06" / 1.5mm
Max. Ø Bundle	35.0mm

→Material and Specifications

- ▼ Cable Ties
 - 18-30 lb Tensile Strength
 - 40-50 lb Tensile Strength
 - Heavy Duty Strength
 - Heavy Duty Wide Strap
 - Q Ties
 - Releasable
 - Releasable Heavy Duty
 - Clamp Ties
 - Double Head
 - Identification
 - Outside Serrated
 - Stainless Steel - 304
 - Stainless Steel - 316
 - High Temp Applications
 - Automatic Tool Cable Ties
 - Swivel Clip Cable Tie
 - Wire Harness Branch Ties
 - Aerial Support Spacer Ties
 - Releasable Grip Ties
- Cable Ties with Fasteners
- Cable Tie Tools
- Clamps and Clips
 - Heatshrink Moulded Shapes
- Mounts
- Heavy Duty Mounts
- Wire Connectors
- Wiring Duct
- Wiring Protection
- Labels, Printers and Software
 - Pre-Terminated Networking
- Copper Network Solutions
- Fiber Network Solutions
- Jacks and Wall Plates
- Racks - Cable Management
- Surface Raceway Systems

Material	Polyamide 4.6 (PA46)
Flammability	UL94 V2
Material Specification	LFH / RoHS
Material Specification	HF
Operating Temperature	-40 °F to +275 °F (-40 °C to +135 °C)
ROHS Conformity	
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No

 Logistic and Packaging

Packaging Type	bag
Pkg. Qty.	1000
Carton Qty.	5000
EAN code	4031026418148
UPC	089306154174

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)