







RECOMMENDED MOUNTING PARAMETERS
1924487-1 AND 1924487-2 ONLY

CONECTOR POSITION	TREE HOLE (THREADED)	ANTI-ROTATION HOLE (THREADED OR UNTHREADED)	THREAD DEPTH (MINIMUM)
2	M8	M6 (5.0mm)	4mm
3	M8	M6 (5.0mm)	6mm
4	M8	M6 (5.0mm)	6mm
6	M8	M6 (5.0mm)	6mm
8	M8	M6 (5.0mm)	8mm
12	M8	M6 (5.0mm)	8mm




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECO-15-014592	09OCT2015	JM	RB
	D1	REVISED PER ECO-15-018109	17DEC2015	DD	RB

- ⚠ MATERIAL: NYLON 6/6, COLOR: BLACK
2. MOUNTING PARAMETERS: SEE RECOMMENDED MOUNTING TABLE ON LEFT SIDE.
- ⚠ AREA TO BE FROSTED APPROXIMATELY WHERE SHOWN.
- ⚠ CAVITY ID.
- ⚠ ANTI-ROTATION POST DIMENSIONS ONLY APPLY TO 1924487-2.



1924487-2

DIMS SAME AS 1924487-1
EXCEPT AS SHOWN




1924487-1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MARKEY 22FEB2008	TE TE Connectivity	
DIMENSIONS:		CHK J. MARKEY 22FEB2008		
mm		APVD J. MARKEY 22FEB2008		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
0 PLC ±		APPLICATION SPEC	NAME RETAINER CLIP, AMPSEAL 16	
1 PLC ±0.5		WEIGHT	SIZE CAGE CODE DRAWING NO	
2 PLC ±0.3		CUSTOMER DRAWING	A100779C=1924487	
3 PLC ±		SCALE 3:1	SHEET 1 OF 2	
4 PLC ±		REV D1		
ANGLES				
FINISH				


1.50 grams	1924487-3
1.65 grams	1924487-2
1.60 grams	1924487-1
WEIGHT (g)	PART NUMBER

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

RECOMMENDED MOUNTING PARAMETERS
1924487-3 ONLY
1924487-3 TO SNAP INTO Ø4.7MM HOLE
IN 3MM STOCK SHEET METAL.



1924487-3
DIMS SAME AS 1924487-1
EXCEPT AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MARKEY 22FEB2008	 TE Connectivity	
		CHK J. MARKEY 22FEB2008		
DIMENSIONS:		APVD J. MARKEY 22FEB2008	NAME RETAINER CLIP, AMPSEAL I6	
mm		PRODUCT SPEC		
		APPLICATION SPEC	SIZE A100779	
		ANGLES	CAGE CODE C=1924487	
		FINISH	DRAWING NO	
			RESTRICTED TO	
MATERIAL	-	WEIGHT	-	-
-	-	CUSTOMER DRAWING	SCALE 3:1	SHEET 2 OF 2
			REV D1	