



0394




0394-0-15-XX-07-XX-10-0
Solder mount in .120 min.
mounting hole

0393




0393-0-15-XX-07-XX-10-0
Solder mount in .144 min.
mounting hole

0391




0391-0-15-XX-07-XX-10-0
Solder mount in .159 min.
mounting hole

9016




9016-0-15-XX-07-XX-10-0
Press-fit in .131 mounting hole

0493




0493-0-15-XX-07-XX-10-0
Press-fit in .144 mounting hole

0490




0490-0-15-XX-07-XX-04-0
Press-fit in .144 mounting hole

0616




0616-0-18-XX-07-XX-10-0
Press-fit in .144 mounting hole

0387




0387-0-15-XX-07-XX-04-0
Solder mount in .063 min.
mounting hole

0370




0370-0-19-XX-07-XX-10-0
#18 Gage crimp barrel

4040




4040-0-19-XX-07-XX-10-0
Wire Termination

0491



0491-0-19-XX-07-XX-04-0
For use in stackable
patch cords

9214



9214-0-15-XX-07-XX-10-0
Solder mount in .083 min.
mounting hole

SPECIFICATIONS

SHELL MATERIAL:
Brass Alloy 360, 1/2 Hard

CONTACT MATERIAL:
Beryllium Copper Alloy 172, HT

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - 1X - XX - 07 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 200μ" TIN/LEAD OVER NICKEL

80 200μ" TIN OVER NICKEL

15 10μ" GOLD OVER NICKEL

SPECIFY CONTACT FINISH:

01 200μ" TIN/LEAD OVER NICKEL

80 200μ" TIN OVER NICKEL

27 30μ" GOLD OVER NICKEL



CONTACT

#07 CONTACT (DATA ON PAGE 225)