

1367551-2 Product Details

[Share](#) [Print](#) [Email](#)


1367551-2

TE Internal Number: 1367551-2

 **Active**

 [View 3D PDF](#)

Z-DOK

 [5 of 6 EU RoHS/ELV Compliant](#) ([Find RoHS Compliant Alternates/Statement of Compliance](#))

Product Highlights:

- Z-DOK+ Product Line
- Connector Style = Receptacle
- 8 Pairs
- 6 Utility Contacts
- Utility Contact Level Location 1 = 1

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [Z-DOK+ ADAPTER BOARD CONNECTOR ASSEMBLY, 8 SIGNAL DI...](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- [Z-DOK and Z-DOK + Connectors](#) (PDF, English)

Application Specifications:

- [Z-DOK and Z-DOK + Connectors](#) (PDF, English)

Instruction Sheets:

- None Available

CAD Files: ([CAD Format & Compression Information](#))

- [2D Drawing](#) (DXF, Version C)
- [3D Model](#) (IGES, Version C)
- [3D Model](#) (STEP, Version C)

[List all Documents](#)

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Line = Z-DOK+
- Mount Angle = Right Angle
- PCB Mount Style = Through Hole (SMT Compatible)

Mechanical Attachment:

- [Number of Pairs](#) = 8

Termination Features:

- Termination Post Length (mm [in]) = 3.10 [0.122]
- Solder Tail Contact Plating = Tin-Lead over Nickel

Body Features:

- PCB Mount Retention Type = Utility Contact

Contact Features:

- Contact Plating, Mating Area, Material = Gold (30)
- Contact Base Material = Copper Alloy
- Utility Contact Material = Phosphor Bronze
- Utility Contact Plating = Gold over Nickel

Housing Features:

- [Connector Style](#) = Receptacle
- Housing Material = Polyester
- Housing Color = Natural

Configuration Features:

- [Number of Utility Contacts](#) = 6
- [Utility Contact Level Location 1](#) = 1
- [Utility Contact Level Location 2](#) = 2
- [Utility Contact Level Location 3](#) = 4
- [Utility Contact Level Location 4](#) = 4
- [Utility Contact Level Location 5](#) = 2
- [Utility Contact Level Location 6](#) = 2

Industry Standards:

- [RoHS/ELV Compliance](#) = ELV compliant, 5 of 6 Compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C

Other:

- Brand = Tyco Electronics

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address

