








RECOMMENDED PCB LAYOUT



- NOTE:
- MATERIAL:
HOUSING: NY6T&PBT+30% GF UL94 V-0
CONTACT: COPPER ALLOY
SHELL: COPPER ALLOY
REAR SHELL: SPCC
 - FINISH:
2.1 CONTACT:
GOLD LASH LAING ON CONTACT REA.
100 μ " MIN.BRIGHT-TIN PLATING ON SOLDER TAIL
AREA, 50 μ " MIN.NICKEL UNDERPLATING OVERALL.
 - 2.2 SHELL:
100 μ " MIN.BRIGHT-TIN PLATING ON SOLDER TAILS.
50 μ " MIN.NICKEL UNDERPLATING OVERALL.
 - 2.3 ISOLATED:SHELL: 100 μ " MIN.NICKEL OVER 50 μ " MIN.CU ENTIRE ISOLATED.
 - 2.4 REAR SHELL: 100 μ " MIN.NICKEL UNDERPLATNG OVERALL.
 - ELECTRICAL CHARACTERISTICS:
CRRENT RATING: 0.5Amper Maximum
VOLTAGE: 30V AC.
CONTACT RETENTION FORCE: 0.7KG F MINIMUM.
CONTACT TESISTANCE: 30 MILLIOHMS MAXIMUM.
INSULATION RESISTANCE: 1000MEGOHMS MINIMUM.
DIELECTRIC WITHSTANDING VOLTAGE: 750V AC AT SEE LEVEL.
PART NO.:

11/01/10	ING		NEW-DWG			AO
DATE	DR.BY	ECN.NO.	DESCRIPTION		MARK	VER.
-TOLERANCES- UNLESS OTHERWISE SPECIFIED			CnC Tech,LLC			
			  TITLE: USB FEMALE A TYPE TRIPLE STACKED RIGHT ANGLE DIP90度			
X.	±0.38	X.X° ±2°	APPD:	PRODUCT NO: 1001-007-01020		
X.X	±0.20	X.XX° ±1°	CHECK:	DATE	SCALE	UNIT
X.XX	±0.10	X.XXX° ±0.5°	DRAW:	2011.01.10	FREE	MM