


Avalanche Energy Rated N-Channel Power MOSFETs

2.0A and 2.5A, 450V-500V
 $r_{DS(on)} = 3.0\Omega$ and 4.0Ω

Features:


- Single pulse avalanche energy rated
- SOA is power-dissipation limited
- Nanosecond switching speeds
- Linear transfer characteristics
- High input impedance

N-CHANNEL ENHANCEMENT MODE



TERMINAL DIAGRAM

TERMINAL DESIGNATION



JEDEC TO-220AB

The IRF820R, IRF821R, IRF822R and IRF823R are advanced power MOSFETs designed, tested, and guaranteed to withstand a specified level of energy in the breakdown avalanche mode of operation. These are n-channel enhancement-mode silicon-gate power field-effect transistors designed for applications such as switching regulators, switching converters, motor drivers, relay drivers, and drivers for high-power bipolar switching transistors requiring high speed and low gate-drive power. These types can be operated directly from integrated circuits.


The IRF-types are supplied in the JEDEC TO-220AB plastic package.

Absolute Maximum Ratings

Parameter	IRF820R	IRF821R	IRF822R	IRF823R	Units
V_{DS} Drain - Source Voltage ①	500	450	500	450	V
V_{DGR} Drain - Gate Voltage ($R_{GS} = 20\text{ K}\Omega$) ①	500	450	500	450	V
$I_D @ T_C = 25^\circ\text{C}$ Continuous Drain Current	2.5	2.5	2.0	2.0	A
$I_D @ T_C = 100^\circ\text{C}$ Continuous Drain Current	1.5	1.5	1.0	1.0	A
I_{DM} Pulsed Drain Current ③	10	10	8.0	8.0	A
V_{GS} Gate - Source Voltage	± 20				V
$P_D @ T_C = 25^\circ\text{C}$ Max. Power Dissipation	40 (See Fig. 14)				W
Linear Derating Factor	0.32 (See Fig. 14)				W/ $^\circ\text{C}$
E_{AS} Single Pulse Avalanche Energy Rating ④	210				mj
T_J Operating Junction and T_{stg} Storage Temperature Range	-55 to 150				$^\circ\text{C}$
Lead Temperature	300 (0.063 in. (1.6mm) from case for 10s)				$^\circ\text{C}$

Electrical Characteristics @ T_c = 25°C (Unless Otherwise Specified)

Parameter	Type	Min.	Typ.	Max.	Units	Test Conditions
BV _{DSS} Drain - Source Breakdown Voltage	IRF820R IRF822R	500	—	—	V	V _{GS} = 0V
	IRF821R IRF823R	450	—	—	V	I _D = 250μA
V _{GS(th)} Gate Threshold Voltage	ALL	2.0	—	4.0	V	V _{DS} = V _{GS} , I _D = 250μA
I _{GSS} Gate-Source Leakage Forward	ALL	—	—	500	nA	V _{GS} = 20V
I _{GSS} Gate-Source Leakage Reverse	ALL	—	—	-500	nA	V _{GS} = -20V
I _{DSS} Zero Gate Voltage Drain Current	ALL	—	—	250	μA	V _{DS} = Max. Rating, V _{GS} = 0V
		—	—	1000	μA	V _{DS} = Max. Rating x 0.8, V _{GS} = 0V, T _c = 125°C
I _{D(on)} On-State Drain Current ②	IRF820R IRF821R	2.5	—	—	A	V _{DS} > I _{D(on)} x R _{DSON(max)} , V _{GS} = 10V
	IRF822R IRF823R	2.0	—	—	A	
R _{DSON} Static Drain-Source On-State Resistance ②	IRF820R IRF821R	—	2.5	3.0	Ω	V _{GS} = 10V, I _D = 1.0A
	IRF822R IRF823R	—	3.0	4.0	Ω	
g _{fs} Forward Transconductance ②	ALL	1.0	1.75	—	S (Ω)	V _{DS} > I _{D(on)} x R _{DSON(max)} , I _D = 1.0A
C _{iss} Input Capacitance	ALL	—	300	—	pF	V _{GS} = 0V, V _{DS} = 25V, f = 1.0 MHz
C _{oss} Output Capacitance	ALL	—	75	—	pF	See Fig. 10
C _{rss} Reverse Transfer Capacitance	ALL	—	20	—	pF	
t _{don} Turn-On Delay Time	ALL	—	30	60	ns	V _{DD} ≈ 0.5BV _{DSS} , I _D = 1.0A, Z _o = 50Ω
t _r Rise Time	ALL	—	25	50	ns	See Fig. 17
t _{doff} Turn-Off Delay Time	ALL	—	30	60	ns	(MOSFET switching times are essentially independent of operating temperature.)
t _f Fall Time	ALL	—	15	30	ns	
Q _g Total Gate Charge (Gate-Source Plus Gate-Drain)	ALL	—	11	26	nC	V _{GS} = 10V, I _D = 3.0A, V _{DS} = 0.8V Max. Rating. See Fig. 18 for test circuit. (Gate charge is essentially independent of operating temperature.)
Q _{gs} Gate-Source Charge	ALL	—	5.0	—	nC	
Q _{gd} Gate-Drain ("Miller") Charge	ALL	—	6.0	—	nC	
L _D Internal Drain Inductance	ALL	—	3.5	—	nH	Measured from the contact screw on tab to center of die.
		—	4.5	—	nH	Measured from the drain lead, 6mm (0.25 in.) from package to center of die.
L _S Internal Source Inductance	ALL	—	7.5	—	nH	Measured from the source lead, 6mm (0.25 in.) from package to source bonding pad.




6

Thermal Resistance

R _{thJC} Junction-to-Case	ALL	—	—	3.12	°C/W	
R _{thCS} Case-to-Sink	ALL	—	1.0	—	°C/W	Mounting surface flat, smooth, and greased.
R _{thJA} Junction-to-Ambient	ALL	—	—	80	°C/W	Free Air Operation

Source-Drain Diode Ratings and Characteristics

I _S Continuous Source Current (Body Diode)	IRF820R IRF821R	—	—	2.5	A	Modified MOSFET symbol showing the integral reverse P-N junction rectifier.
	IRF822R IRF823R	—	—	2.0	A	
I _{SM} Pulse Source Current (Body Diode) ③	IRF820R IRF821R	—	—	10	A	
	IRF822R IRF823R	—	—	8.0	A	
V _{SD} Diode Forward Voltage ②	IRF820R IRF821R	—	—	1.6	V	T _c = 25°C, I _S = 2.5A, V _{GS} = 0V
	IRF822R IRF823R	—	—	1.5	V	T _c = 25°C, I _S = 2.0A, V _{GS} = 0V
t _{rr} Reverse Recovery Time	ALL	—	600	—	ns	T _J = 150°C, I _F = 2.5A, dI _F /dt = 100A/μs
Q _{RR} Reverse Recovered Charge	ALL	—	3.5	—	μC	T _J = 150°C, I _F = 2.5A, dI _F /dt = 100A/μs
t _{on} Forward Turn-on Time	ALL	Intrinsic turn-on time is negligible. Turn-on speed is substantially controlled by L _S + L _D .				



① T_J = 25°C to 150°C. ② Pulse Test: Pulse width ≤ 300μs, Duty Cycle ≤ 2%.
 ③ Repetitive Rating: Pulse width limited by max. junction temperature. See Transient Thermal Impedance Curve (Fig. 5).
 ④ V_{DD} = 5V, starting T_J = 25°C, L = 60mH, R_{gs} = 25Ω, I_{peak} = 2.5A. See figures 15, 16.

IRF820R, IRF821R, IRF822R, IRF823R




Fig. 1 - Typical Output Characteristics




Fig. 2 - Typical Transfer Characteristics




Fig. 3 - Typical Saturation Characteristics




Fig. 4 - Maximum Safe Operating Area




Fig. 5 - Maximum Effective Transient Thermal Impedance, Junction-to-Case Vs. Pulse Duration

IRF820R, IRF821R, IRF822R, IRF823R




Fig. 6 – Typical Transconductance Vs. Drain Current




Fig. 7 – Typical Source-Drain Diode Forward Voltage




Fig. 8 – Breakdown Voltage Vs. Temperature




Fig. 9 – Normalized On-Resistance Vs. Temperature




Fig. 10 – Typical Capacitance Vs. Drain-to-Source Voltage




Fig. 11 – Typical Gate Charge Vs. Gate-to-Source Voltage

6

IRF820R, IRF821R, IRF822R, IRF823R




Fig. 12 — Typical On-Resistance Vs. Drain Current




Fig. 13 — Maximum Drain Current Vs. Case Temperature




Fig. 14 — Power Vs. Temperature Derating Curve




Fig. 15 — Unclamped Energy Test Circuit




Fig. 16 — Unclamped Energy Waveforms




Fig. 17 — Switching Time Test Circuit




Fig. 18 — Gate Charge Test Circuit