


TUNING FORK CRYSTAL UNITS (Cylinder Type)

RoHS Compliant Optional




CFS308·CFS206·CFS145·CFV206



FEATURES

- Best suited for portable devices with low current consumption.
- For a clock source in digital equipment.

DIMENSION [mm]



STANDARD SPECIFICATIONS

Item	Model	CFS308	CFS206	CFS145	CFV206	Conditions
Nominal Frequency	f_0	32.768kHz			30kHz~100kHz	Need to contact us for the available frequency in CFV-206
Frequency Tolerance	$\Delta f/f_0$	$\pm 20\text{ppm}$			$\pm 30\text{ppm}$	at 25°C
Load capacitance	C_L	12.5pF				Need to specify your requirement
Operating Temperature Range	T_{OPR}	$-20^\circ\text{C} \sim +70^\circ\text{C}$				
Storage Temperature Range	T_{STR}	$-40^\circ\text{C} \sim +85^\circ\text{C}$				
Turnover Temperature	T_M	$25^\circ\text{C} \pm 5^\circ\text{C}$				See figure 2 in P4
Temperature Coefficient	β	$-0.034 \pm 0.006\text{ppm}/^\circ\text{C}^2$				
Motional (series) resistance	R_1	35K Ω Max.		40K Ω Max.	50K Ω Max.	at 25°C
Level of drive	D_L	1 μW Max.				
Aging (first year)	$\Delta f/f_0$	$\pm 3\text{ppm}$ Max.			$\pm 5\text{ppm}$ Max.	$25^\circ\text{C} \pm 3^\circ\text{C}$
Quality Factor	Q	85000 Typ.	70000 Typ.	85000 Typ.	70000~100000 Typ.	Depend on frequency
Shunt capacitance	C_0	1.6pF Typ.	1.35pF Typ.	1.00pF Typ.	0.8~1.7pF Typ.	Depend on frequency