

## Patch panels - VS-PP-R-1XRJ45/RJ45 - 1404391

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Patch panel, RJ45, DIN rail mounting, IP20, 2 slots, socket/socket, CAT5e, option of shielding via jumpers



Ethernet

### Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	60.610 g
Custom tariff number	85366990
Country of origin	Germany

### Technical data

#### Mechanical characteristics

Connection method	Female
Number of slots	2
Minimum external conductor diameter	5 mm
Maximum external conductor diameter	8.5 mm
Weight	60.9 g
Flammability rating according to UL 94	V0

#### Ambient conditions

Ambient temperature (operation)	- 15 °C ... 50 °C
---------------------------------	-------------------

#### Material data

Contact material	Copper alloy
Housing material	PVC

#### Electrical characteristics

Number of positions	8
---------------------	---

## Patch panels - VS-PP-R-1XRJ45/RJ45 - 1404391

### Technical data

#### Electrical characteristics

Transmission characteristics (category)	CAT5 (IEC 11801:2002)
Rated current	1 A
Rated voltage (III/3)	60 V


#### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Drawings

Patch panels - VS-PP-R-1XRJ45/RJ45 - 1404391

Dimensional drawing



RJ45 patch panel

Classifications

eCl@ss

eCl@ss 4.0	27140815
eCl@ss 4.1	27140815
eCl@ss 5.0	19030109
eCl@ss 5.1	19030109
eCl@ss 6.0	19170107

## Patch panels - VS-PP-R-1XRJ45/RJ45 - 1404391

### Classifications

#### eCl@ss

eCl@ss 7.0	19170112
------------	----------

#### ETIM

ETIM 2.0	EC000200
ETIM 3.0	EC001128
ETIM 4.0	EC001128
ETIM 5.0	EC001128

#### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501