

# MC74LVX126

## Quad Bus Buffer

### With 5V-Tolerant Inputs

The MC74LVX126 is an advanced high speed CMOS quad bus buffer. The inputs tolerate voltages up to 7.0 V, allowing the interface of 5.0 V systems to 3.0 V systems.

The MC74LVX126 requires the 3-state control input (OE) to be set Low to place the output into the high impedance state.

#### Features




- High Speed:  $t_{PD} = 4.4$  ns (Typ) at  $V_{CC} = 3.3$  V
- Low Power Dissipation:  $I_{CC} = 4$   $\mu$ A (Max) at  $T_A = 25^\circ\text{C}$
- Power Down Protection Provided on Inputs
- Balanced Propagation Delays
- Low Noise:  $V_{OLP} = 0.5$  V (Max)
- Pin and Function Compatible with Other Standard Logic Families
- Latchup Performance Exceeds 300 mA
- ESD Performance: Human Body Model >2000 V  
Machine Model >200 V
- These devices are available in Pb-free package(s). Specifications herein apply to both standard and Pb-free devices. Please see our website at [www.onsemi.com](http://www.onsemi.com) for specific Pb-free orderable part numbers, or contact your local ON Semiconductor sales office or representative.



ON Semiconductor®

<http://onsemi.com>

#### MARKING DIAGRAMS



|          |   |           |
|----------|---|-----------|
| A        | = | Assembly  |
| Location |   |           |
| L, WL    | = | Wafer Lot |
| Y        | = | Year      |
| W, WW    | = | Work      |
| Week     |   |           |

#### ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 4 of this data sheet.

# MC74LVX126




Figure 1. 14-Lead Pinout (Top View)




Figure 2. Logic Diagram

## PIN NAMES

| Pins | Function             |
|------|----------------------|
| OEn  | Output Enable Inputs |
| Dn   | Data Inputs          |
| On   | 3-State Outputs      |

## FUNCTION TABLE

| INPUTS |    | OUTPUTS |
|--------|----|---------|
| OEn    | Dn | On      |
| H      | L  | L       |
| H      | H  | H       |
| L      | X  | Z       |

H = High Voltage Level; L = Low Voltage Level; Z = High Impedance State; X = High or Low Voltage Level and Transitions Are Acceptable, for I<sub>CC</sub> reasons, DO NOT FLOAT Inputs

## MAXIMUM RATINGS

| Symbol           | Parameter                                       | Value                        | Unit |
|------------------|-------------------------------------------------|------------------------------|------|
| V <sub>CC</sub>  | DC Supply Voltage                               | −0.5 to +7.0                 | V    |
| V <sub>in</sub>  | DC Input Voltage                                | −0.5 to +7.0                 | V    |
| V <sub>out</sub> | DC Output Voltage                               | −0.5 to V <sub>CC</sub> +0.5 | V    |
| I <sub>IK</sub>  | Input Diode Current                             | −20                          | mA   |
| I <sub>OK</sub>  | Output Diode Current                            | ±20                          | mA   |
| I <sub>out</sub> | DC Output Current, per Pin                      | ±25                          | mA   |
| I <sub>CC</sub>  | DC Supply Current, V <sub>CC</sub> and GND Pins | ±50                          | mA   |
| P <sub>D</sub>   | Power Dissipation                               | 180                          | mW   |
| T <sub>stg</sub> | Storage Temperature                             | −65 to +150                  | °C   |

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

## RECOMMENDED OPERATING CONDITIONS

| Symbol           | Parameter                                | Min | Max             | Unit |
|------------------|------------------------------------------|-----|-----------------|------|
| V <sub>CC</sub>  | DC Supply Voltage                        | 2.0 | 3.6             | V    |
| V <sub>in</sub>  | DC Input Voltage                         | 0   | 5.5             | V    |
| V <sub>out</sub> | DC Output Voltage                        | 0   | V <sub>CC</sub> | V    |
| T <sub>A</sub>   | Operating Temperature, All Package Types | −40 | +125            | °C   |
| Δt/ΔV            | Input Rise and Fall Time                 | 0   | 100             | ns/V |

# MC74LVX126

## DC ELECTRICAL CHARACTERISTICS

| Symbol          | Parameter                                                                            | Test Conditions                                                                                   | V <sub>CC</sub><br>V | T <sub>A</sub> = 25°C |            |                    | T <sub>A</sub> = ≤ 85°C |                    | T <sub>A</sub> = ≤ 125°C |                    | Unit |
|-----------------|--------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|----------------------|-----------------------|------------|--------------------|-------------------------|--------------------|--------------------------|--------------------|------|
|                 |                                                                                      |                                                                                                   |                      | Min                   | Typ        | Max                | Min                     | Max                | Min                      | Max                |      |
| V <sub>IH</sub> | High-Level Input Voltage                                                             |                                                                                                   | 2.0<br>3.0<br>3.6    | 1.5<br>2.0<br>2.4     |            |                    | 1.5<br>2.0<br>2.4       |                    | 1.5<br>2.0<br>2.4        |                    | V    |
| V <sub>IL</sub> | Low-Level Input Voltage                                                              |                                                                                                   | 2.0<br>3.0<br>3.6    |                       |            | 0.5<br>0.8<br>0.8  |                         | 0.5<br>0.8<br>0.8  |                          | 0.5<br>0.8<br>0.8  | V    |
| V <sub>OH</sub> | High-Level Output Voltage<br>(V <sub>in</sub> = V <sub>IH</sub> or V <sub>IL</sub> ) | I <sub>OH</sub> = -50 μA<br>I <sub>OH</sub> = -50 μA<br>I <sub>OH</sub> = -4 mA                   | 2.0<br>3.0<br>3.0    | 1.9<br>2.9<br>2.58    | 2.0<br>3.0 |                    | 1.9<br>2.9<br>2.48      |                    |                          | 1.9<br>2.9<br>2.34 | V    |
| V <sub>OL</sub> | Low-Level Output Voltage<br>(V <sub>in</sub> = V <sub>IH</sub> or V <sub>IL</sub> )  | I <sub>OL</sub> = 50 μA<br>I <sub>OL</sub> = 50 μA<br>I <sub>OL</sub> = 4 mA                      | 2.0<br>3.0<br>3.0    |                       | 0.0<br>0.0 | 0.1<br>0.1<br>0.36 |                         | 0.1<br>0.1<br>0.44 |                          | 0.1<br>0.1<br>0.52 | V    |
| I <sub>in</sub> | Input Leakage Current                                                                | V <sub>in</sub> = 5.5 V or GND                                                                    | 3.6                  |                       |            | ±0.1               |                         | ±1.0               |                          | ±1.0               | μA   |
| I <sub>OZ</sub> | Maximum Three-State Leakage Current                                                  | V <sub>in</sub> = V <sub>IL</sub> or V <sub>IH</sub><br>V <sub>out</sub> = V <sub>CC</sub> or GND | 3.6                  |                       |            | ±0.25              |                         | ±2.5               |                          | ±5.0               | μA   |
| I <sub>CC</sub> | Quiescent Supply Current                                                             | V <sub>in</sub> = V <sub>CC</sub> or GND                                                          | 3.6                  |                       |            | 4.0                |                         | 40                 |                          | 40                 | μA   |

## AC ELECTRICAL CHARACTERISTICS (Input t<sub>r</sub> = t<sub>f</sub> = 3.0 ns)

| Symbol                                   | Parameter                            | Test Conditions                                                                                              | T <sub>A</sub> = 25°C |      |            | T <sub>A</sub> = ≤ 85°C |            | T <sub>A</sub> = ≤ 125°C |            | Unit |
|------------------------------------------|--------------------------------------|--------------------------------------------------------------------------------------------------------------|-----------------------|------|------------|-------------------------|------------|--------------------------|------------|------|
|                                          |                                      |                                                                                                              | Min                   | Typ  | Max        | Min                     | Max        | Min                      | Max        |      |
| t <sub>PLH</sub> ,<br>t <sub>PHL</sub>   | Propagation Delay<br>Input to Output | V <sub>CC</sub> = 2.7 V    C <sub>L</sub> = 15 pF                                                            |                       | 5.5  | 10.1       | 1.0                     | 13.5       | 1.0                      | 15.0       | ns   |
|                                          |                                      | V <sub>CC</sub> = 3.3 ± 0.3 V    C <sub>L</sub> = 50 pF                                                      |                       | 7.5  | 13.6       | 1.0                     | 17.0       | 1.0                      | 19.0       |      |
| t <sub>PZL</sub> ,<br>t <sub>PZH</sub>   | Output Enable Time<br>OE to O        | V <sub>CC</sub> = 2.7 V    C <sub>L</sub> = 15 pF                                                            |                       | 5.3  | 9.3        | 1.0                     | 12.5       | 1.0                      | 15.5       | ns   |
|                                          |                                      | R <sub>L</sub> = 1 kΩ    C <sub>L</sub> = 50 pF                                                              |                       | 7.8  | 12.8       | 1.0                     | 16.0       | 1.0                      | 18.5       |      |
| t <sub>PLZ</sub> ,<br>t <sub>PHZ</sub>   | Output Disable Time<br>OE to O       | V <sub>CC</sub> = 3.3 ± 0.3 V    C <sub>L</sub> = 15 pF                                                      |                       | 4.0  | 5.6        | 1.0                     | 7.5        | 1.0                      | 9.5        | ns   |
|                                          |                                      | R <sub>L</sub> = 1 kΩ    C <sub>L</sub> = 50 pF                                                              |                       | 6.5  | 9.1        | 1.0                     | 11.0       | 1.0                      | 13.0       |      |
| t <sub>PLZ</sub> ,<br>t <sub>PHZ</sub>   | Output Disable Time<br>OE to O       | V <sub>CC</sub> = 2.7 V    C <sub>L</sub> = 50 pF                                                            |                       | 10.0 | 15.7       | 1.0                     | 19.0       | 1.0                      | 21.0       | ns   |
|                                          |                                      | R <sub>L</sub> = 1 kΩ    C <sub>L</sub> = 50 pF                                                              |                       | 8.3  | 11.2       | 1.0                     | 13.0       | 1.0                      | 15.0       |      |
| t <sub>OSHL</sub> ,<br>t <sub>OSLH</sub> | Output-to-Output Skew<br>(Note 1)    | V <sub>CC</sub> = 2.7 V    C <sub>L</sub> = 50 pF<br>V <sub>CC</sub> = 3.3 ± 0.3 V    C <sub>L</sub> = 50 pF |                       |      | 1.5<br>1.5 |                         | 1.5<br>1.5 |                          | 1.5<br>1.5 | ns   |

1. Skew is defined as the absolute value of the difference between the actual propagation delay for any two separate outputs of the same device. The specification applies to any outputs switching in the same direction, either HIGH-to-LOW (t<sub>OSHL</sub>) or LOW-to-HIGH (t<sub>OSLH</sub>); parameter guaranteed by design.

## CAPACITIVE CHARACTERISTICS

| Symbol           | Parameter                              | T <sub>A</sub> = 25°C |     |     | T <sub>A</sub> = ≤ 85°C |     | T <sub>A</sub> = ≤ 125°C |     | Unit |
|------------------|----------------------------------------|-----------------------|-----|-----|-------------------------|-----|--------------------------|-----|------|
|                  |                                        | Min                   | Typ | Max | Min                     | Max | Min                      | Max |      |
| C <sub>in</sub>  | Input Capacitance                      |                       | 4   | 10  |                         | 10  |                          | 10  | pF   |
| C <sub>out</sub> | Maximum Three-State Output Capacitance |                       | 6   |     |                         |     |                          |     | pF   |
| C <sub>PD</sub>  | Power Dissipation Capacitance (Note 2) |                       | 14  |     |                         |     |                          |     | pF   |

2. C<sub>PD</sub> is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation: I<sub>CC(OPR)</sub> = C<sub>PD</sub> • V<sub>CC</sub> • f<sub>in</sub> + I<sub>CC</sub> / 4 (per bit). C<sub>PD</sub> is used to determine the no-load dynamic power consumption; P<sub>D</sub> = C<sub>PD</sub> • V<sub>CC</sub><sup>2</sup> • f<sub>in</sub> + I<sub>CC</sub> • V<sub>CC</sub>.

# MC74LVX126

**NOISE CHARACTERISTICS** (Input  $t_r = t_f = 3.0$  ns,  $C_L = 50$  pF,  $V_{CC} = 3.3$  V, Measured in SOIC Package)

| Symbol    | Characteristic                           | $T_A = 25^\circ\text{C}$ |      | Unit |
|-----------|------------------------------------------|--------------------------|------|------|
|           |                                          | Typ                      | Max  |      |
| $V_{OLP}$ | Quiet Output Maximum Dynamic $V_{OL}$    | 0.3                      | 0.5  | V    |
| $V_{OLV}$ | Quiet Output Minimum Dynamic $V_{OL}$    | -0.3                     | -0.5 | V    |
| $V_{IHD}$ | Minimum High Level Dynamic Input Voltage |                          | 2.0  | V    |
| $V_{ILD}$ | Maximum Low Level Dynamic Input Voltage  |                          | 0.8  | V    |

## ORDERING INFORMATION

| Device        | Package   | Shipping†        |
|---------------|-----------|------------------|
| MC74LVX126D   | SOIC-14   | 55 Units / Rail  |
| MC74LVX126M   | SOEIAJ-14 | 50 Units / Rail  |
| MC74LVX126MEL | SOEIAJ-14 | 2000 Tape & Reel |

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

## SWITCHING WAVEFORMS




Figure 3.






Figure 4.

## TEST CIRCUITS



\*Includes all probe and jig capacitance

Figure 5. Propagation Delay Test Circuit




\*Includes all probe and jig capacitance

Figure 6. Three-State Test Circuit

# MC74LVX126

## PACKAGE DIMENSIONS

PDIP-14  
P SUFFIX  
CASE 646-06  
ISSUE N




### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. DIMENSION L TO CENTER OF LEADS WHEN FORMED PARALLEL.
4. DIMENSION B DOES NOT INCLUDE MOLD FLASH.
5. ROUNDED CORNERS OPTIONAL.

| DIM | INCHES    |       | MILLIMETERS |       |
|-----|-----------|-------|-------------|-------|
|     | MIN       | MAX   | MIN         | MAX   |
| A   | 0.715     | 0.770 | 18.16       | 18.80 |
| B   | 0.240     | 0.260 | 6.10        | 6.60  |
| C   | 0.145     | 0.185 | 3.69        | 4.69  |
| D   | 0.015     | 0.021 | 0.38        | 0.53  |
| F   | 0.040     | 0.070 | 1.02        | 1.78  |
| G   | 0.100 BSC |       | 2.54 BSC    |       |
| H   | 0.052     | 0.095 | 1.32        | 2.41  |
| J   | 0.008     | 0.015 | 0.20        | 0.38  |
| K   | 0.115     | 0.135 | 2.92        | 3.43  |
| L   | 0.290     | 0.310 | 7.37        | 7.87  |
| M   | 10 °      |       | 10 °        |       |
| N   | 0.015     | 0.039 | 0.38        | 1.01  |

SOIC-14  
D SUFFIX  
CASE 751A-03  
ISSUE G



### NOTES:


1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSIONS A AND B DO NOT INCLUDE MOLD PROTRUSION.
4. MAXIMUM MOLD PROTRUSION 0.15 (0.006) PER SIDE.
5. DIMENSION D DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.127 (0.005) TOTAL IN EXCESS OF THE D DIMENSION AT MAXIMUM MATERIAL CONDITION.

| DIM | MILLIMETERS |      | INCHES    |       |
|-----|-------------|------|-----------|-------|
|     | MIN         | MAX  | MIN       | MAX   |
| A   | 8.55        | 8.75 | 0.337     | 0.344 |
| B   | 3.80        | 4.00 | 0.150     | 0.157 |
| C   | 1.35        | 1.75 | 0.054     | 0.068 |
| D   | 0.35        | 0.49 | 0.014     | 0.019 |
| F   | 0.40        | 1.25 | 0.016     | 0.049 |
| G   | 1.27 BSC    |      | 0.050 BSC |       |
| J   | 0.19        | 0.25 | 0.008     | 0.009 |
| K   | 0.10        | 0.25 | 0.004     | 0.009 |
| M   | 0 °         |      | 7 °       |       |
| P   | 5.80        | 6.20 | 0.228     | 0.244 |
| R   | 0.25        | 0.50 | 0.010     | 0.019 |

# MC74LVX126

## PACKAGE DIMENSIONS

SOEIAJ-14  
M SUFFIX  
CASE 965-01  
ISSUE O



### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH OR PROTRUSIONS AND ARE MEASURED AT THE PARTING LINE. MOLD FLASH OR PROTRUSIONS SHALL NOT EXCEED 0.15 (0.006) PER SIDE.
4. TERMINAL NUMBERS ARE SHOWN FOR REFERENCE ONLY.
5. THE LEAD WIDTH DIMENSION (b) DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE 0.08 (0.003) TOTAL IN EXCESS OF THE LEAD WIDTH DIMENSION AT MAXIMUM MATERIAL CONDITION. DAMBAR CANNOT BE LOCATED ON THE LOWER RADIUS OR THE FOOT. MINIMUM SPACE BETWEEN PROTRUSIONS AND ADJACENT LEAD TO BE 0.46 (0.018).

| DIM            | MILLIMETERS |       | INCHES    |       |
|----------------|-------------|-------|-----------|-------|
|                | MIN         | MAX   | MIN       | MAX   |
| A              | ---         | 2.05  | ---       | 0.081 |
| A <sub>1</sub> | 0.05        | 0.20  | 0.002     | 0.008 |
| b              | 0.35        | 0.50  | 0.014     | 0.020 |
| c              | 0.18        | 0.27  | 0.007     | 0.011 |
| D              | 9.90        | 10.50 | 0.390     | 0.413 |
| E              | 5.10        | 5.45  | 0.201     | 0.215 |
| e              | 1.27 BSC    |       | 0.050 BSC |       |
| H <sub>E</sub> | 7.40        | 8.20  | 0.291     | 0.323 |
| L              | 0.50        | 0.85  | 0.020     | 0.033 |
| L <sub>E</sub> | 1.10        | 1.50  | 0.043     | 0.059 |
| M              | 0 °         | 10 °  | 0 °       | 10 °  |
| Q <sub>1</sub> | 0.70        | 0.90  | 0.028     | 0.035 |
| Z              | ---         | 1.42  | ---       | 0.056 |

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## PUBLICATION ORDERING INFORMATION

### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor  
P.O. Box 61312, Phoenix, Arizona 85062-1312 USA  
Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada  
Fax: 480-829-7709 or 800-344-3867 Toll Free USA/Canada  
Email: [orderlit@onsemi.com](mailto:orderlit@onsemi.com)

N. American Technical Support: 800-282-9855 Toll Free  
USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center  
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051  
Phone: 81-3-5773-3850

ON Semiconductor Website: <http://onsemi.com>

Order Literature: <http://www.onsemi.com/litorder>

For additional information, please contact your  
local Sales Representative.