

4

3


2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
		REL PER 0G3A-0928-04		18NOV04	JR	TM

AMP WIRE RANGE
16-14 AWG STRANDED



- 1 WIRE INSULATION DIA 3.81 [.150] TO 6.35 [.250].
- 2 BODY & SLEEVE: COPPER PER ASTM B152 INSULATION : NYLON
- 3 BODY & SLEEVE: TIN PLATE PER ASTM B545 INSULATION : YELLOW
- 4 PREPRODUCTION - FASR REQUIRED

50	LOOSE PIECE	4 696730-1
QTY	PACKAGE TYPE	PART NUMBER

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 105° C	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 04OCT04	Tyco Electronics Corporation Harrisburg, PA 17105		
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: 600V MAX 1000V MAX (FIXTURE OR SIGN)	DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK T MICHIELUTTI 04OCT04	NAME SPLICE, BUTT, PIDG, WIRE SIZE: 16-14HD AWG		
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 1.04-2.62mm² [2,050-5,180] STRANDED		0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD T MICHIELUTTI 04OCT04	APPLICATION SPEC		
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		FINISH	PRODUCT SPEC	SIZE A3	CAGE CODE 00779	DRAWING NO C-696730
			MATERIAL - 2	- 3	WEIGHT -	RESTRICTED TO		
			CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV B