


DATASHEET

C0603X5R100-475MNE

GENERAL PURPOSE CERAMIC CAPACITORS (C SERIES)
0603, X5R, 10V, 4.7uF, $\pm 20\%$, 100% matte Tin(Sn) over Nickel



VENKEL LTD.



SIZE SPECIFICATIONS units: inches

Length:	0.063
Width:	0.032
T(max):	0.040
Min E/B:	0.008
Size(EIA):	0603

COMPONENT SPECIFICATIONS

Category:	Ceramic Capacitors
Series:	General Purpose (C Series)
Size:	0603
Dielectric:	X5R
Voltage:	10V
Capacitance:	4.7uF
Tolerance:	$\pm 20\%$
Termination:	100% matte Tin(Sn) over Nickel
Packaging:	E
Quantity per Reel:	4,000

DIELECTRIC SPECIFICATIONS

Temperature Coefficient:	$0 \pm 15\% \Delta^\circ\text{C MAX}$
Temperature Voltage Coefficient	X5R not applicable
Ageing:	2.5% per decade hour, typical
Withstanding Voltage:	2.5 times VDCW
Operating Temp:	-55°C to $+85^\circ\text{C}$
Dissipation Factor:	See C Series Datasheet

ENVIRONMENTAL INFORMATION

RoHS Status	6 of 6 Compliant
REACH Status	Compliant
Halogen Status	Halogen Free
Conflict Mineral Status	Conflict Mineral Free
Moisture Sensitivity Level	MSL1

REFLOW PROFILE

Max Reflow Temperature	260 $^\circ\text{C}$
Number of Reflow Cycles	2
Time at Max Reflow Temp.	10 sec

REEL DIMENSIONS units: mm

Tape	B min	C	A(7")	A(13")	D Min	N Min	G	T max
8mm	0.30	$13 \pm .05$	178 ± 2.0	330 ± 2.0	20.20	50.00	10 ± 1.5	14.90

TAPING SPECIFICATIONS units: mm

A	B	W	F	E	Po
1.10 ± 0.2	1.90 ± 0.2	8.0 ± 0.2	3.5 ± 0.1	1.75 ± 0.1	4.0 ± 0.1
Pz	D	T	P	To	T(E)
$2.0 \pm 0.05 - 0.0$	1.5 ± 0.1	1.15 MAX	4.0 ± 0.1		