



COLOR STRIPE RUNNING LENGTH OF HOUSING
LOCATION APPROXIMATELY AS SHOWN
(SEE CHART ON SHEET 2) SEE NOTE 8




NOTES:

1. MATERIAL: HOUSING - 6/6 NYLON, UL94V-2
TERMINALS - BRASS
2. FINISH: SEE CHART ON SHEET 2
3. PRODUCT SPECIFICATION: PS-7241
4. PARTS ARE BULK PACKAGED.
5. WARPAGE OVER ENTIRE LENGTH NOT TO EXCEED .015/(0.38).
6. CHAIN CUT-OFF (TYP. BOTH ENDS)
WO/FLANGE - FLUSH TO $\pm .015/(0.38)$ FROM DATUM C.
7. THIS PART CONFORMS TO CLASS B REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
8. COLOR STRIPE NOT PRESENT ON PARTS WITH BLACK HOUSINGS.



RECOMMENDED PC BOARD

ADD NOTE 8 EC NO: UCP2012-3293 DRAWN:MMSTROH 2012/04/03 CHKD:MKIPER 2012/04/04 APPR:FSMTH 2012/04/05		DESCRIPTION	QUALITY SYMBOLS F _A =0 F _E =0 F _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 2:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
					mm	INCH	DRAWN BY	DATE	TITLE EDGE CONNECTOR, KK .156/ (3.96), INSULATION DISPLACEMENT		
				4 PLACES	± ---	± ---	WRL	1979/02/14			
				3 PLACES	± ---	± .010	CHECKED BY	DATE			
				2 PLACES	± 0.25	± .014	WRL	1979/02/14	MOLEX INCORPORATED		
				1 PLACE	± 0.35	± ---	APPROVED BY	DATE			
				ANGULAR ±1/2°							
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
						SEE CHART		SDA-7241-****		1 OF 2	
U1		REV		SIZE B	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

09-07-2032	A-7241-03LB	3	NONE	7241-3B	BLACK	40591-L(154)	.000100/(0.00254) MIN. TIN OVER .000050/(0.00127) MIN. NICKEL	NONE
09-07-2031	A-7241-03L	3	NONE	7241-3	NATURAL	40591-L(154)	.000100/(0.00254) MIN. TIN OVER .000050/(0.00127) MIN. NICKEL	NONE
PART NUMBER	ENGINEERING NUMBER	CIRCUITS	TERMINAL VOID IN CIRCUIT	HOUSING NUMBER	HOUSING COLOR	TERMINAL NUMBER	TERMINAL PLATING	CENTER RIB LOCATED BETWEEN CIRCUIT

COLOR IDENTIFICATION		TYPE OF WIRE TERMINATED
ASSEMBLY SUFFIX NO.	COLOR	{ALL WIRES HAVE A MAXIMUM INSULATION DIAMETER OF.080/(.2.03)}
-*NA*	YELLOW	#18 GA SOLID OR FUSED STRANDED
-*NM*	RED	#20 GA SOLID OR FUSED STRANDED (18 GA. STRANDED WIRE)
-*NL*	BLUE	#20 GA STRANDED WIRE
-*ND*	GREEN	*26 & *27 GA STRANDED,FUSED STRANDED & SOLID WIRE OR *24 GA STRANDED WIRE
-*NJ*	BLACK	#24 & #22 GA SOLID OR FUSED STRANDED (*22 GA STRANDED WIRE)

3	.632+.006/(16.05±0.15)
CIRCUITS	DIM "A"

CHANGE PLATING EC NO: UCP2012-1821 C U	REV	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
			=0 =0 =0	mm	INCH	DRAWN BY	DATE	TITLE EDGE CONNECTOR, KK .156/ (3.96), ISULATION DISPLACEMENT				
				4 PLACES	± ---	± ---	WRL					1979/02/14
				3 PLACES	± ---	± ---	CHECKED BY					DATE
				2 PLACES	± ---	± ---	WRL					1979/02/14
				1 PLACE	± ---	± ---	APPROVED BY	DATE	MOLEX INCORPORATED			
			ANGULAR ± ---°		MATERIAL NO.		DOCUMENT NO.				SHEET NO.	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SDA-7241-****				2 OF 2	
			SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

09-07-2031