




## Specifications

- **Certifications\*:** UL, CSA, VDE
- **Dielectric Strength:** 1,000V (minimum)
- **Insulation Resistance:** 100 Megohms (minimum)
- **Base Material:** Nylon
- **Actuator Material:** Nylon

\* Due to ongoing technological advances, consult factory for certification specifics.



**C 70 1 - R - B - B - 0**

| SERIES |               | CIRCUIT <sup>1</sup> |                                                | RATING <sup>2</sup> |                                                                   | ACTUATOR STYLE              |        | BASE COLOR <sup>3</sup>                   |       |
|--------|---------------|----------------------|------------------------------------------------|---------------------|-------------------------------------------------------------------|-----------------------------|--------|-------------------------------------------|-------|
| RGSC   | STANDARD BASE | A                    | OFF-NONE-ON SINGLE POLE                        | 20                  | 15A 250VAC<br>20A 125VAC                                          | P                           | PADDLE | B                                         | BLACK |
| RGSB   | METAL BRACKET | B                    | ON-NONE-ON SINGLE POLE                         |                     | 3/4HP 125-250VAC                                                  | R                           | ROCKER | W                                         | WHITE |
| RGSE   | EUROPEAN BASE | C                    | OFF-NONE-ON DOUBLE POLE                        | 21                  | 15A 250 VAC<br>20A 125VAC                                         | ACTUATOR COLOR <sup>3</sup> |        | ROCKER FACE IMPRINTED LEGEND <sup>4</sup> |       |
|        |               | D                    | ON-NONE-ON DOUBLE POLE                         | 57                  | 10A 250VAC 3/4HP<br>15A 125VAC 3/4HP<br>6A 277VAC 3/4HP           | B                           | BLACK  | 0 NO LEGEND                               |       |
|        |               | E                    | POLE 1<br>ON-NONE-ON<br>POLE 2<br>OFF-NONE-ON  | 70                  | 15A 250VAC<br>20A 125VAC<br>3/4HP 125-250VAC<br>16(6)A 250VAC T85 | W                           | WHITE  | A OFF-ON (VERTICAL)                       |       |
|        |               | F                    | POLE 1<br>ON-NONE-OFF<br>POLE 2<br>OFF-NONE-ON | 71                  | 15A 250VAC<br>20A 125VAC<br>16(6)A 250VAC T85                     |                             |        | B OFF-ON (HORIZONTAL)                     |       |
|        |               |                      |                                                | TERMINATION         |                                                                   |                             |        | D O-I (HORIZONTAL)                        |       |
|        |               |                      |                                                | 0 SOLDER LUG        |                                                                   |                             |        | E O-I (VERTICAL)                          |       |
|        |               |                      |                                                | 1 .250TAB (QC)      |                                                                   |                             |        | F ON-OFF (VERTICAL)                       |       |
|        |               |                      |                                                | 5 WIRE LEAD         |                                                                   |                             |        | G ON-OFF (HORIZONTAL)                     |       |

4 White is standard with dark actuators; black is standard with light actuators.