

6

5

4



3

2



1

NOTES:

1. MATERIAL : HEADER: POLYESTER, GLASS FILLED.
PIN : BRASS
2. FINISH:
.000100/(0.00254) MIN. TIN OVER
.000050/(0.00127) MIN. NICKEL UNDERPLATE.
3. PARTS CONFORM TO PRODUCT SPECIFICATION PS-42219-0001.
4. PACKAGING: SEE LEGEND.
5. KINK DIRECTION:
2 THROUGH 7 CKTS: ADJACENT PINS KINKED IN
OPPOSING DIRECTIONS.
8 THROUGH 15 CKTS: TWO END PINS ON EACH END
KINKED IN THE SAME DIRECTION.
CENTER PINS WITHOUT KINKS.
6. PARTS CONFORM TO CLASS 'B' REQUIREMENTS OF COSMETIC
SPEC PS-45499-002.

CIRCUIT NO. 1
IDENTIFIEROPTIONAL
VOIDED CIRCUIT
SEE CHART FOR
LOCATION

CIRCUIT 1

.098±.002
(2.50±.05) TYP.

CIRCUIT 1

.037±.002
(0.94±.05) DIA.PCB HOLE LAYOUT: COMPONENT SIDE
RECOMMENDED PCB THICKNESS: .062/(1.57)

A-42267-N*-*-*

NO OF CKTS ↑ ↑ ↑

HOUSING NO. ↑

PACKAGING METHOD
BLANK = BULK PACK PER PK-42249-0001

VOID LOCATION ↑

NO. OF CKTS.	KINK LOCATION	DIM. A	DIM. B
2	1,2,	.292/(7.42)	.098/(2.50)
3	1,2,3	.391/(9.92)	.197/(5.00)
4	1,2,3,4	.489/(12.42)	.295/(7.50)
5	1,2,3,4,5	.587/(14.92)	.394/(10.00)
6	1,2,3,4,5,6	.685/(17.40)	.492/(12.50)
7	1,2,3,4,5,6,7	.783/(19.90)	.591/(15.00)
8	1,2,7,8	.882/(22.40)	.689/(17.50)
9	1,2,8,9	.980/(24.90)	.787/(20.00)
10	1,2,9,10	1.079/(27.40)	.886/(22.50)
11	1,2,10,11	1.177/(29.90)	.984/(25.00)
12	1,2,11,12	1.276/(32.40)	1.083/(27.50)
13	1,2,12,13	1.374/(34.90)	1.181/(30.00)
14	1,2,13,14	1.472/(37.40)	1.280/(32.50)
15	1,2,14,15	1.571/(39.90)	1.378/(35.00)

ADD BULK PK SPEC EC NO: UCP2013-2919 DRWN:MKIPPER 2013/01/17 CHK'D:ANDERSON 2013/01/17 APPR:FSM TH 2013/01/29				DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	
			mm			INCH	DRAWN BY GUZIK	DATE 01/17/89	TITLE 2.5 MM HEADER ASSEMBLY					
		4 PLACES	± ---			± ---	CHECKED BY EDGLEY	DATE 01/17/89						
		3 PLACES	± ---			± .010	APPROVED BY LENZ		DATE 01/17/89	DOCUMENT NO. SDA-42267-* SHEET NO. 1 OF 4				
		2 PLACES	± 0.25			± .014	MATERIAL NO. SEE CHART							
Q3		1 PLACE	± 0.36			± ---	SIZE A		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
		0 PLACE	±			±								
		ANGULAR ±1/2°												
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												

[illegible]

[illegible]

[illegible]