

A B C D E F


REVISIONS				
SYM	ZONE	ECN, ERN NO.	DATE	APPRD.
F		PROPOSAL	JUL18/12	L.CHAN
G		PROPOSAL	JUL31/12	L.CHAN

1


2

1


2




FRONT VIEW



SIDE VIEW



RECOMMENDED PANEL CUTOUT



RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)

MATERIALS:

PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0,
COLOR: BLACK

CONTACTS:

PHOSPHOR BRONZE
PLATING: 50 μ" [1.27 MICRONS]
MIN. GOLD ON MATING SURFACES.
50 μ" [1.27 MICRONS]
MIN. NICKEL UNDERPLATE
100 μ" [2.54 MICRONS]
MIN. MATTE TIN ON CONTACT TAILS.



PART NUMBER: RJHSE-5080

4

4

TOLERANCE ARE : DECIMALs .X ±.025 .XX ±.020 .XXX ±.015		ANGLEs X° ±3.0° .X° ±2.0° .XX° ±1.0°		DRAWN PAUL WANG		DATE 06/03/28		Amphenol Canada Corp.							
				DESIGNED											
				CHECKED CHIGOW		06/03/28		TITLE SINGLE-PORT HIGH SPEED RJ45 MODULAR JACK, WITHOUT LED, 8 POS. 8 CONTACTS, NO SHIELD-RoHS COMPLIANT							
				I. E. APPRD.											
				Q. A. APPRD.											
				DWG. APPRD.											
				ENG. REL. NO.											
				REF.				DWG		DRAWING NO.		REV.			
				DIMENSIONS ARE IN INCHES [mm]		CODE ID. NO. 03554				P-RJHSE-5080		G			
								SCALE:		WT. -----		SURF. -----		SHEET 1 OF 1	

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION
MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING
PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

A B C D E F