

1

2

3

4

5

6

7

8

REFERENCE SPECIFICATIONS

-NFC 93425 (in compliance with HE 507)

PHYSICAL CHARACTERISTICS

-INSULATOR MATERIAL: THERMOPLASTIC UL94V0

-CONTACT MATERIAL: PHOSPHOR BRONZE(SIGNAL CONTACT)

BRASS (POWERS CONTACT)

-ACCESSORIES: BRASS

-SHELLS: STEEL

ELECTRICAL CHARACTERISTICS

-NOMINAL CURRENT: 7.5A (SIGNAL CONTACT)

30A or 40A (POWER CONTACT)

-CONTACT RESISTANCE: <=7.3 m Ohms(SIGNAL and POWER)

-CONTACT/CONTACT : >=1000 V

-CONTACT/GROUND : >=1200 V

-INSULATION RESISTANCE: >=5000 MOhms

ENVIRONMENTAL CHARACTERISTICS

- CLIMATIC CATEGORY: 55/125/21

TEMPERATURE RANGE -55°C TO +125°C

DAMP HEAT STEADY STATE 21 DAYS

SALT SPRAY 48 HOURS

MECHANICAL CHARACTERISTICS

- RETENTION AGAINST TORQUE: - Threaded insert: 0.7 N.m minimum

- Female screw : 0.5 N.m minimum

NOTE RoHS INFORMATION

- The "LF" products meet european union Directives and other country regulations as described in GS-22-008.

- The housing will withstand exposure to 260°C peak temperature for 3.5 seconds in a wave solder application with a 1.6mm minimum thick circuit board. See application notes/procedures if they are available.

- Termination plating spec:

- Signal contacts: Ni + Gold

- Power contacts: Ni 1.27µmi+Sn 2.5 to 7.5µ,pure bright

- Active area plating spec:

- Signal and power contacts: Ni + Gold

- Shell plating :2 to 4µm Cu + nickel + 3 to 10µmm Sn,pure bright

- Accessories: Sn pure bright + nickel

- Packaging spec: See GS-14-920

Series

Shell size: E A B C D (see sheet 3)

Front accessory definition (see sheet 2)

blank:without accessory

L :threaded insert M3

O :threaded insert UNC 4-40

V :female screw UNC 4-40

Layout of contacts (see sheet 3)

Contacts

S :Socket

Termination type

5 Right angle/Europe standard

Plating

00 200 matings/unmatings

43 500 matings/unmatings

PCB accessories definition(see sheet 2)

A :without accessory

H :Metal brackets+harpoons for PCB 2.40mm

G :Metal brackets+harpoons for PCB 1.60mm

M :Metal brackets

Power contacts

00 :Not fitted with power contact (signal contacts always fitted)

30 :Fitted with power contacts 30 Amp.

40 :Fitted with power contacts 40 Amp.

DBL13W3S500G30LF

See note RoHS

TABLE 1:PCB HOLE DIAMETERS

POWER CONTACTS			ACCESSORIES	SIGNAL CONTACT
30 A	2.00	Ø2.40	Ø3.10	Ø0.9 min
40 A	2.80	Ø3.10		
Max current power	ØA ^{+0.1} ₀	PCB HOLE ±0.1	PCB HOLE ±0.1	PCB HOLE

rev

ecn no

dr

date

A

LS05-0101

MPE

2005-10-11

B

LS06-0208

LGO

2006-12-12

C

LS07-0273

MPE

2007/10/31

D

F09-0092

LSA

2009/09/16

E

F10-0060

LSA

2010/06/01

-

-

-

-

-

-

-

-

Dr

M PESSON

2005-10-11

Eng

P LEGARE

2005-10-11

Chr

Appr

surface

ISO 1302

- ✓

tolerance std

ISO 406

ISO 1101

projection

ISO 1101

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED

ANGULAR

0° ±2°

LINEAR

0.X ±0.3

0.XX ±0.1

0.XXX ±0.05

size

A2

Scale

2:1

ECN

F10-0060

Product family

-

Spec ref

-

www.fciconnect.com

title

SUB FEMALE DMW EUROPE

mixed power right angled solder

catalog no

-

dwg no

C01-8639-2300

Rev.

E

sheet 1 of 7

FCI


Copyright FCI.

REV E - 2006-03-28

PDM: Rev:E

STATUSReleased





Printed: Oct 01, 2010



5W1

LAYOUT AND CONNECTOR DIMENSIONS

For PCB hole diameters see table I sheet I







Floating signal contacts

11W1

LAYOUT AND CONNECTOR DIMENSIONS







For PCB hole diameters see table I sheet I



7W2

LAYOUT AND CONNECTOR DIMENSIONS

For PCB hole diameters see table I sheet I


SIDE VIEW FOR ALL LAYOUTS
(except size D)VIEW WITHOUT POWERS
CONTACTSVIEW WITH POWERS
CONTACTS

Copyright FCI.

www.fciconnect.com			surface	✓	tolerance std	projection	mm
			ISO 1302		ISO 406 ISO 1101		
			TOLERANCES UNLESS OTHERWISE SPECIFIED				
Dr	M PESSON	2005-10-11	ANGULAR		0.X	±0.3	size
Eng	P LEGARE	2005-10-11		LINEAR	0.XX	±0.1	A2
Chr			0° ±2°		0.XXX	±0.05	ECN
Appr			Product family		Spec ref		
FCI			SUB FEMALE DMW EUROPE			dwg no	
			mixed power right angled solder			C01-8639-2300	
			catalog no			CUSTOMER	
						sheet 4 of 7	
						Rev.	
						E	


13W3

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I













9W4

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



17W2

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table I sheet I



Floating signal contacts


www.fciconnect.com			surface ISO 1302		- ✓ tolerance std ISO 406 ISO 1101		projection 		mm 				
			TOLERANCES UNLESS OTHERWISE SPECIFIED										
Dr	M PESSON	2005-10-11	ANGULAR		LINEAR		0.X		±0.3		size A2	Scale 2:1	
Eng	P LEGARE	2005-10-11					0.XX		±0.1				
Chr			0° ±2°		0.XXX		±0.05		ECN		F10-0060		
Appr			Product family					- Spec ref					
			title SUB FEMALE DMW EUROPE mixed power right angled solder					dwg no C01-8639-2300					Rev. E
			catalog no					- CUSTOMER					




Copyright FCI.

REV E - 2006-03-28

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table 1 sheet 1




LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table 1 sheet 1



www.fciconnect.com			surface 		tolerance std ISO 1302 ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	M PESSON	2005-10-11	ANGULAR	LINEAR	0.X	±0.3	size A2	Scale 2:1		
Eng	P LEGARE	2005-10-11			0.XX	±0.1		ECN	F10-0060	
Chg					0° ±2°	0.XXX				
Appr			Product family			-	Spec ref			
		title SUB FEMALE DMW EUROPE mixed power right angled solder				dwg no C01-8639-2300			Rev	
									E	
catalog no		-				CUSTOMER		sheet 6 of 7		


21W A4

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table 1 sheet 1




25W 3

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table 1 sheet 1



24W 7

LAYOUT AND CONNECTOR DIMENSIONS
For PCB hole diameters see table 1 sheet 1



www.fciconnect.com		surface ISO 1302	tolerance std ISO 406	projection ISO 1101	mm
		TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	M PESSON	2005-10-11	ANGULAR	0.X	±0.3
Eng	P LEGARE	2005-10-11	LINEAR	0.XX	±0.1
Chr			0° ±2°	0.XXX	±0.05
Appr			Product family	-	Spec ref
FCI		title SUB FEMALE DMW EUROPE			Rev.
		mixed power right angled solder			E
		catalog no			
		- CUSTOMER			sheet 7 of 7