

L-7104SRD-14V

SUPER BRIGHT RED


Features

- LOW POWER CONSUMPTION.
- POPULAR T-1 DIAMETER PACKAGE.
- GENERAL PURPOSE LEADS.
- RELIABLE AND RUGGED.
- LONG LIFE - SOLID STATE RELIABILITY.
- AVAILABLE ON TAPE AND REEL.
- 14V INTERNAL RESISTOR.
- RoHS COMPLIANT.

Description

The Super Bright Red source color devices are made with Gallium Aluminum Arsenide Red Light Emitting Diode.

Package Dimensions



Notes:

1. All dimensions are in millimeters (inches).
2. Tolerance is $\pm 0.25(0.01")$ unless otherwise noted.
3. Lead spacing is measured where the leads emerge from the package.
4. Specifications are subject to change without notice.

Kingbright

Selection Guide

Part No.	Dice	Lens Type	I _v (mcd) V=14V		Viewing Angle θ1/2
			Min.	Typ.	
L-7104SRD-14V	SUPER BRIGHT RED (GaAlAs)	RED DIFFUSED	28	90	40°

Note:

1. θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

Electrical / Optical Characteristics at T_A=25°C

Symbol	Parameter	Device	Typ.	Max.	Units	Test Conditions
λ _{peak}	Peak Wavelength	Super Bright Red	660		nm	V _F =14V
λD	Dominant Wavelength	Super Bright Red	640		nm	V _F =14V
Δλ1/2	Spectral Line Half-width	Super Bright Red	20		nm	V _F =14V
I _F	Forward Current	Super Bright Red	10.5	13.5	mA	V _F =14V
I _R	Reverse Current	Super Bright Red		10	uA	V _R = 5V


Absolute Maximum Ratings at T_A=25°C

Parameter	Super Bright Red	Units
Power dissipation	160	mW
Forward Voltage	16	V
Reverse Voltage	5	V
Operating/Storage Temperature	-40°C To +85°C	
Lead Solder Temperature [1]	260°C For 3 Seconds	
Lead Solder Temperature [2]	260°C For 5 Seconds	

Notes:





2. 2mm below package base.

3. 3mm below package base.



Super Bright Red

L-7104SRD-14V



Remarks:

If special sorting is required (e.g. binning based on luminous intensity, or wavelength), the typical accuracy of the sorting process is as follows:

1. Wavelength: +/-1nm

2. Luminous Intensity: +/-15%

Note: Accuracy may depend on the sorting parameters.