


DIMENSIONS AND PERMISSIBLE RIPPLE CURRENT



Lead Spacing and Diameter (mm)

øD	5	6.3	8	10	13	16	18	22	25
ød	0.6	0.6	0.6	0.6	0.8	0.8	0.8	1.0	1.0
α	1.5	1.5	1.5	1.5	2.0	2.0	2.0	2.0	2.0
β	0.5	0.5	0.5	0.5	1.0	1.0	1.0	1.0	1.0

Value (μF)	Working Voltage; Dimensions: øD x L (mm); Ripple Current: mA/RMS @ 120Hz, 85°C															
	6.3		10		16		25		35		50		63		100	
	øD x L	mA	øD x L	mA	øD x L	mA	øD x L	mA	øD x L	mA	øD x L	mA	øD x L	mA	øD x L	mA
0.1											5 x 12	1.5	5 x 12	3.0	5 x 12	3.0
0.22											5 x 12	3.5	5 x 12	4.5	5 x 12	4.5
0.33											5 x 12	5.0	5 x 12	7.5	5 x 12	7.5
0.47											5 x 12	6.0	5 x 12	9.0	5 x 12	9.0
1											5 x 12	10	5 x 12	15	5 x 12	15
2.2											5 x 12	20	5 x 12	30	5 x 12	30
3.3											5 x 12	30	5 x 12	36	6.3 x 12	41
4.7											5 x 12	42	5 x 12	44	6.3 x 12	50
6.8											5 x 12	50	5 x 13	55		
10									5 x 12	55	6.3 x 12	65	6.3 x 12	68	6.3 x 12	72
22					5 x 12	71	5 x 12	76	6.3 x 12	88	6.3 x 12	96	6.3 x 14	109	8 x 16	133
33			5 x 12	78	5 x 12	88	6.3 x 12	100	6.3 x 14	115	6.3 x 14	126	8 x 16	154	10 x 17	190
47	5 x 12	87	5 x 12	94	6.3 x 12	111	6.3 x 12	119	6.3 x 14	138	8 x 16	174	10 x 17	214	10 x 21	237
100	6.3 x 12	136	6.3 x 12	145	6.3 x 16	174	8 x 16	215	8 x 16	232	10 x 17	298	10 x 21	326	13 x 22	377
220	6.3 x 14	215	6.3 x 16	231	8 x 16	298	8 x 16	319	10 x 17	401	10 x 21	459	13 x 2			