

4



3

2



1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
A1							
			A3	RELEASED ASPER ECR-09-012227	29-May-09	GG	TS

CONTACT ARRANGEMENT:
VIEW FROM CONNECTING SIDE




CONTACT ARRANGEMENT:
VIEW FROM TERMINATION SIDE



NOTES

- SUITABLE CRIMP CONTACTS: SERIES HN.D
CUSTOMER DRAWING: 1105050
OUTER DIMENSIONS OF INSULATION:MAX.Ø4mm
- SUITABLE MODULE FIXING FRAME: SERIES HVS SIZE 3 TO 8
CUSTOMER DRAWING: 1103250
- SUITABLE INSERTION TOOL:
CUSTOMER DRAWING: 1102855
- SUITABLE EXTRACTION TOOL:
CUSTOMER DRAWING: 1102855
- STANDARDS:
DIN EN 61984; DIN EN 60664-1
- PACKAGING:
10 SETS IN A CARTON,PRE-MOUNTED



SCALE 1:1

PN 0-1 AS SHOWN

PN 0-1	DESCRIPTION	MATERIAL	SURFACE	COLOR	NOTE	ITEM NO
1	SCREW PAN HEAD	STEEL			ISO 7045 A2	6
1	SPRING WASHER,A3	STEEL	ZINC PLATED		DIN 137	5
1	CLOSING 3-6mm	ZINC				4
1	CONTACT INSERT MALE	PA66-GF25		BLACK		3
1	CLOSING 6-9mm	ZINC				2
1	SHIELD BARREL MALE	ZINC				1

HVS-TX.HN.D.4.Sti.C

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN SCHNEIDER 21.02.2006	Tyco Electronics AMP GmbH 53757 Sankt Augustin, Germany			
DIMENSIONS: mm		CHK A.GAST 21.02.2006	NAME SHIELD BARREL MALE HVS-TX.HN.D.4.STI			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ISO 8075 DIN ISO 2768 mH-E DIN 16901-120		APVD T.SCHNURPFIL 21.02.2006	SIZE A3			
0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES		PRODUCT SPEC 108-74086	CAGE CODE 00779			
MATERIAL		APPLICATION SPEC 114-74088	DRAWING NO 1103283			
FINISH		WEIGHT	RESTRICTED TO			
CUSTOMER DRAWING		SCALE 5:1	SHEET 1 OF 1			
			REV A3			