




Home> Products > MICRO SWITCH™ Toggle Switches> TW > Product Page

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback



Actual product appearance may vary.

TW Series Toggle Switch, 2 pole, 2 position, Solder terminal, Locking Lever

Features

Save space and weight
SPDT and DPDT circuitry
Temperature range: -85° F to +160° F (-65° C to +71° C)
Sealed bushing versions
Choice of 1/8 in. or 15/32 in. bushing
Color tab available on 15/32 in. bushing
UL recognized

Potential Applications

Industrial machinery and equipment
Military and commercial aviation
Construction equipment
Test instruments
Agricultural machinery
Process control
Medical instrumentation

Description

MICRO SWITCH™ miniature toggle switches in two bushing sizes. Molded in terminals are plated for soldering. Momentary and maintained circuitry closures available. Special on-on-on circuitries are also available. Pull-to-unlock levers prevent accidental operation.

Supporting Documentation

- Accessory: Seals
- Accessory: Nuts
- Engineering Drawing

Product Specifications	
Circuitry/Operating action	<div><div>Keyway Position</div><div>Opposite Keyway Position</div></div>
Product Type	MICRO SWITCH™ Toggle Switch
Lever Lock	<div><div></div><div>Locked out of center position</div></div>
Ampere/Voltage Range (Resistive Load)	0.1 A to 5.0 A at 0.5 Vdc to 28 Vdc, 0.1 A to 5.0 A at 0.5 Vac to 115 Vac
Circuitry	DPDT
Action	2 position
Mounting	Bushing 15/32 in
Termination	Solder
Lever Type	Locking
UL/CSA Rating Code	L117: 5 A at 125 Vac
Comment	Shorter than standard mushroom lever
Availability	Global
UNSPSC Code	30211908
UNSPSC Commodity	30211908 Toggle switches
Series Name	TW

My Links

- Login to iCOM
- Login as Rep/AD
- Login as Guest
- Login to Digital University

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search