




PART NO.

MC34 Series

## REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Ramya	08/10/09	Naveen	08/10/09	Farnell	22/10/09





PART NO.

MC34 Series

## REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Ramya	08/10/09	Naveen	08/10/09	Farnell	22/10/09

**Specifications:**

Current rating : 1.0A ac, dc.  
Voltage rating : 125V ac, dc.  
Maximum contact resistance : 20mΩ.  
Minimum insulation resistance : 100MΩ.  
Withstanding resistance : 250V ac for one minute.  
Operating temperature range : -40°C to +85°C.

**Material and Finish:**

Insulator : High temperature plastic.  
Contact : Copper alloy.  
Finish : Tin plated.

**Specification Table**

Description	Number of Position	A	B	C	Part Number
-------------	--------------------	---	---	---	-------------