









P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)



NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; BLACK
- CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- THREADED SPACER CLIPS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: Ø3.1± 0.1; PCB THICKNESS 2,3mm
- COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: DSH1XSRAA19X CONEC ABC



Directive 2002/95/EC
„RoHS“
Compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance			scale: 2:1 (5:1)		
				ISO 2768-m			material: SEE NOTES		
				date	name		title: D-SUB HD FEMALE 15pos. SOLDER PIN STRAIGHT with threaded spacer clip		
				drawn 23.11.10	Henneboel				
				appd. 23.11.10	Koch				
				norm					
				d-old		dwg no:		Inventor 10	DIN-A3 sh: 1
	a	Origin				16K1A2742			
	rev.	description	date			name	part no: DSH1XSRAA19X		