

# Octal Buffer/Line Driver with 3-State Outputs

## 74VHC244


### General Description

The VHC244 is an advanced high speed CMOS octal bus buffer fabricated with silicon gate CMOS technology. It achieves high speed operation similar to equivalent Bipolar Schottky TTL while maintaining the CMOS low power dissipation. The VHC244 is a non-inverting 3-STATE buffer having two active-LOW output enables. These devices are designed to be used as 3-STATE memory address drivers, clock drivers, and bus oriented transmitter/receivers.

An input protection circuit ensures that 0 V to 5.5 V can be applied to the input pins without regard to the supply voltage. This device can be used to interface 5 V to 3 V systems and two supply systems such as battery back up. This circuit prevents device destruction due to mismatched supply and input voltages.


### Features

- High Speed:  $t_{PD}$  3.9 ns (typ) at  $V_{CC}$  5 V
- High Noise Immunity:  $V_{NIH} = V_{NIL} = 28\% V_{CC}$  (min)
- Power Down Protection is Provided on All Inputs
- Low Noise:  $V_{OLP} = 0.6$  V (typ)
- Low Power Dissipation:  $I_{CC} = 4 \mu A$  (max) @  $T_A = 25^\circ C$
- Pin and Function Compatible with 74HC244
- These are Pb-Free Devices



TSSOP20, 4.4x6.5  
CASE 948AQ

### MARKING DIAGRAMS




#### TSSOP-20

- XXXXXX = Specific Device Code  
A = Assembly Location  
L = Wafer Lot  
Y = Year  
W = Work Week  
▪ = Pb-Free Package

(Note: Microdot may be in either location)

### CONNECTION DIAGRAM



### PIN DESCRIPTION

| Pin Names                          | Description          |
|------------------------------------|----------------------|
| $\overline{OE}_1, \overline{OE}_2$ | Output Enable Inputs |
| $I_0-I_7$                          | Inputs               |
| $O_0-O_7$                          | 3-State Outputs      |

### ORDERING INFORMATION

See detailed ordering and shipping information on page 4 of this data sheet.

# 74VHC244

## LOGIC SYMBOL




Figure 1. Logic Symbol

## TRUTH TABLES

| Inputs            |       | Outputs               |
|-------------------|-------|-----------------------|
| $\overline{OE}_1$ | $I_n$ | (Pins 12, 14, 16, 18) |
| L                 | L     | L                     |
| L                 | H     | H                     |
| H                 | X     | Z                     |

| Inputs            |       | Outputs           |
|-------------------|-------|-------------------|
| $\overline{OE}_2$ | $I_n$ | (Pins 3, 5, 7, 9) |
| L                 | L     | L                 |
| L                 | H     | H                 |
| H                 | X     | Z                 |

NOTE: H = HIGH Voltage Level  
L = LOW Voltage Level  
X = Immaterial  
Z = High Impedance

## ABSOLUTE MAXIMUM RATINGS

| Symbol        | Parameter                                       |                        | Value                  | Unit |
|---------------|-------------------------------------------------|------------------------|------------------------|------|
| $V_{CC}$      | DC Supply Voltage                               |                        | -0.5 to +6.5           | V    |
| $V_{IN}$      | DC Input Voltage                                |                        | -0.5 to +6.5           | V    |
| $V_{OUT}$     | DC Output Voltage                               |                        | -0.5 to $V_{CC} + 0.5$ | V    |
| $I_{IN}$      | DC Input Current, per Pin                       |                        | $\pm 20$               | mA   |
| $I_{OUT}$     | DC Output Current, per Pin                      |                        | $\pm 25$               | mA   |
| $I_{CC}$      | DC Supply Current, $V_{CC}$ and GND Pins        |                        | $\pm 75$               | mA   |
| $I_{IK}$      | Input Clamp Current                             |                        | -20                    | mA   |
| $I_{OK}$      | Output Clamp Current                            |                        | $\pm 20$               | mA   |
| $T_{STG}$     | Storage Temperature Range                       |                        | -65 to +150            | °C   |
| $T_L$         | Lead Temperature, 1 mm from Case for 10 Seconds |                        | 260                    | °C   |
| $T_J$         | Junction Temperature under Bias                 |                        | +150                   | °C   |
| $\theta_{JA}$ | Thermal Resistance (Note 2)                     |                        | 150                    | °C/W |
| $P_D$         | Power Dissipation in Still Air at 25°C          |                        | 833                    | mW   |
| MSL           | Moisture Sensitivity                            |                        | Level 1                |      |
| $F_R$         | Flammability Rating                             | Oxygen Index: 28 to 34 | UL 94 V-0 @ 0.24 in    |      |
| $V_{ESD}$     | ESD Withstand Voltage (Note 3)                  | Human Body Model       | 2000                   | V    |
|               |                                                 | Charged Device Model   | N/A                    |      |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Applicable to devices with outputs that may be tristated.
2. Measured with minimum pad spacing on an FR4 board, using 76 mm-by-114 mm, 2-ounce copper trace no air flow per JESD51-7.
3. HBM tested to EIA / JESD22-A114-A. CDM tested to JESD22-C101-A.

## RECOMMENDED OPERATING CONDITIONS

| Symbol                          | Parameter                  |                                  | Min | Max             | Unit |
|---------------------------------|----------------------------|----------------------------------|-----|-----------------|------|
| V <sub>CC</sub>                 | DC Supply Voltage          |                                  | 2.0 | 5.5             | V    |
| V <sub>IN</sub>                 | DC Input Voltage (Note 4)  |                                  | 0   | 5.5             | V    |
| V <sub>OUT</sub>                | DC Output Voltage (Note 4) |                                  | 0   | V <sub>CC</sub> | V    |
| T <sub>A</sub>                  | Operating Temperature      |                                  | −40 | +85             | °C   |
| t <sub>r</sub> , t <sub>f</sub> | Input Rise or Fall Rate    | V <sub>CC</sub> = 3.0 V to 3.6 V | 0   | 100             | ns/V |
|                                 |                            | V <sub>CC</sub> = 4.5 V to 5.5 V | 0   | 20              |      |

Functional operation above the stresses listed in the Recommended Operating Ranges is not implied. Extended exposure to stresses beyond the Recommended Operating Ranges limits may affect device reliability.

4. Unused inputs must always be tied to an appropriate logic voltage level (e.g., either GND or  $V_{CC}$ ). Unused outputs must be left open.

## DC ELECTRICAL CHARACTERISTICS

| Symbol   | Parameter                        | Conditions                                                | $V_{CC}$ (V)                      | $T_A = 25\text{ °C}$ |      |                     | $T_A = -40\text{ °C to }+85\text{ °C}$ |                     | Unit          |
|----------|----------------------------------|-----------------------------------------------------------|-----------------------------------|----------------------|------|---------------------|----------------------------------------|---------------------|---------------|
|          |                                  |                                                           |                                   | Min                  | Typ  | Max                 | Min                                    | Max                 |               |
| $V_{IH}$ | HIGH Level Input Voltage         |                                                           | 2.0                               | 1.5                  | –    | –                   | 1.5                                    | –                   | V             |
|          |                                  |                                                           | 3.0–5.5                           | $0.7 \times V_{CC}$  | –    | –                   | $0.7 \times V_{CC}$                    | –                   |               |
| $V_{IL}$ | LOW Level Input Voltage          |                                                           | 2.0                               | –                    | –    | 0.50                | –                                      | 0.50                | V             |
|          |                                  |                                                           | 3.0–5.5                           | –                    | –    | $0.3 \times V_{CC}$ | –                                      | $0.3 \times V_{CC}$ |               |
| $V_{OH}$ | HIGH Level Output Voltage        | $V_{IN} = V_{IH}$ or $V_{IL}$                             | $I_{OH} = -50\text{ }\mu\text{A}$ | 2.0                  | 1.9  | 2.0                 | –                                      | 1.9                 | V             |
|          |                                  |                                                           |                                   | 3.0                  | 2.9  | 3.0                 | –                                      | 2.9                 |               |
|          |                                  |                                                           |                                   | 4.5                  | 4.4  | 4.5                 | –                                      | 4.4                 |               |
|          |                                  |                                                           | $I_{OH} = -4\text{ mA}$           | 3.0                  | 2.58 | –                   | –                                      | 2.48                |               |
|          |                                  |                                                           |                                   | 4.5                  | 3.94 | –                   | –                                      | 3.80                |               |
| $V_{OL}$ | LOW Level Output Voltage         | $V_{IN} = V_{IH}$ or $V_{IL}$                             | $I_{OL} = 50\text{ }\mu\text{A}$  | 2.0                  | –    | 0.0                 | 0.1                                    | –                   | V             |
|          |                                  |                                                           |                                   | 3.0                  | –    | 0.0                 | 0.1                                    | –                   |               |
|          |                                  |                                                           |                                   | 4.5                  | –    | 0.0                 | 0.1                                    | –                   |               |
|          |                                  |                                                           | $I_{OL} = 4\text{ mA}$            | 3.0                  | –    | –                   | 0.36                                   | –                   |               |
|          |                                  |                                                           |                                   | 4.5                  | –    | –                   | 0.36                                   | –                   |               |
| $I_{OZ}$ | 3-STATE Output Off-State Current | $V_{IN} = V_{IH}$ or $V_{IL}$ ; $V_{OUT} = V_{CC}$ or GND | 5.5                               | –                    | –    | $\pm 0.25$          | –                                      | $\pm 2.5$           | $\mu\text{A}$ |
| $I_{IN}$ | Input Leakage Current            | $V_{IN} = 5.5\text{ V}$ or GND                            | 0–5.5                             | –                    | –    | $\pm 0.1$           | –                                      | $\pm 1.0$           | $\mu\text{A}$ |
| $I_{CC}$ | Quiescent Supply Current         | $V_{IN} = V_{CC}$ or GND                                  | 5.5                               | –                    | –    | 4.0                 | –                                      | 40.0                | $\mu\text{A}$ |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

## NOISE CHARACTERISTICS

| Symbol             | Parameter                                | Conditions           | $V_{CC}$ (V) | $T_A = 25\text{ °C}$ |        | Unit |
|--------------------|------------------------------------------|----------------------|--------------|----------------------|--------|------|
|                    |                                          |                      |              | Typ                  | Limits |      |
| $V_{OLP}$ (Note 5) | Quiet Output Maximum Dynamic $V_{OL}$    | $C_L = 50\text{ pF}$ | 5.0          | 0.6                  | 0.9    | V    |
| $V_{OLV}$ (Note 5) | Quiet Output Minimum Dynamic $V_{OL}$    | $C_L = 50\text{ pF}$ | 5.0          | -0.6                 | -0.9   | V    |
| $V_{IHD}$ (Note 5) | Minimum HIGH Level Dynamic Input Voltage | $C_L = 50\text{ pF}$ | 5.0          | –                    | 3.5    | V    |
| $V_{ILD}$ (Note 5) | Maximum LOW Level Dynamic Input Voltage  | $C_L = 50\text{ pF}$ | 5.0          | –                    | 1.5    | V    |

5. Parameter guaranteed by design.

# 74VHC244

## AC ELECTRICAL CHARACTERISTICS

| Symbol                                   | Parameter                     | Conditions              |                        | V <sub>CC</sub> (V) | T <sub>A</sub> = 25 °C |      |      | T <sub>A</sub> = -40 °C to +85 °C |      | Unit |
|------------------------------------------|-------------------------------|-------------------------|------------------------|---------------------|------------------------|------|------|-----------------------------------|------|------|
|                                          |                               |                         |                        |                     | Min                    | Typ  | Max  | Min                               | Max  |      |
| t <sub>PLH</sub> ,<br>t <sub>PHL</sub>   | Propagation Delay Time        |                         | C <sub>L</sub> = 15 pF | 3.3 ±0.3            | –                      | 5.8  | 8.4  | 1.0                               | 10.0 | ns   |
|                                          |                               |                         | C <sub>L</sub> = 50 pF |                     | –                      | 8.3  | 11.9 | 1.0                               | 13.5 |      |
|                                          |                               |                         | C <sub>L</sub> = 15 pF | 5.0 ±0.5            | –                      | 3.9  | 5.5  | 1.0                               | 6.5  |      |
|                                          |                               |                         | C <sub>L</sub> = 50 pF |                     | –                      | 5.4  | 7.5  | 1.0                               | 8.5  |      |
| t <sub>PZL</sub> ,<br>t <sub>PZH</sub>   | 3–STATE Output Enable Time    | R <sub>L</sub> = 1 kΩ   | C <sub>L</sub> = 15 pF | 3.3 ±0.3            | –                      | 6.6  | 10.6 | 1.0                               | 12.5 | ns   |
|                                          |                               |                         | C <sub>L</sub> = 50 pF |                     | –                      | 9.1  | 14.1 | 1.0                               | 16.0 |      |
|                                          |                               |                         | C <sub>L</sub> = 15 pF | 5.0 ±0.5            | –                      | 4.7  | 7.3  | 1.0                               | 8.5  |      |
|                                          |                               |                         | C <sub>L</sub> = 50 pF |                     | –                      | 6.2  | 9.3  | 1.0                               | 10.5 |      |
| t <sub>PLZ</sub> ,<br>t <sub>PHZ</sub>   | 3–STATE Output Disable Time   | R <sub>L</sub> = 1 kΩ   | C <sub>L</sub> = 50 pF | 3.3 ±0.3            | –                      | 10.3 | 14.0 | 1.0                               | 16.0 | ns   |
|                                          |                               |                         | C <sub>L</sub> = 50 pF | 5.0 ±0.5            | –                      | 6.7  | 9.2  | 1.0                               | 10.5 |      |
| t <sub>OSLH</sub> ,<br>t <sub>OSHL</sub> | Output to Output Skew         | (Note 6)                | C <sub>L</sub> = 50 pF | 3.3 ±0.3            | –                      | –    | 1.5  | –                                 | 1.5  | ns   |
|                                          |                               |                         | C <sub>L</sub> = 50 pF | 5.0 ±0.5            | –                      | –    | 1.0  | –                                 | 1.0  |      |
| C <sub>IN</sub>                          | Input Capacitance             | V <sub>CC</sub> = Open  |                        |                     | –                      | 4    | 10   | –                                 | 10   | pF   |
| C <sub>OUT</sub>                         | Output Capacitance            | V <sub>CC</sub> = 5.0 V |                        |                     | –                      | 6    | –    | –                                 | –    | pF   |
| C <sub>PD</sub>                          | Power Dissipation Capacitance | (Note 7)                |                        |                     | –                      | 19   | –    | –                                 | –    | pF   |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

6. Parameter guaranteed by design. t<sub>OSLH</sub> – |t<sub>PLHmax</sub> – t<sub>PLHmin</sub>|; t<sub>OSHL</sub> – |t<sub>PHLmax</sub> – t<sub>PHLmin</sub>|

7. C<sub>PD</sub> is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation: I<sub>CC</sub> (OPR.) = C<sub>PD</sub> \* V<sub>CC</sub> \* f<sub>IN</sub> + I<sub>CC</sub>/8 (per bit).


## ORDERING INFORMATION

| Device       | Marking    | Package              | Shipping <sup>†</sup>    |
|--------------|------------|----------------------|--------------------------|
| 74VHC244MTC  | VHC<br>244 | TSSOP20<br>(Pb-Free) | 75 Units / Tube          |
| 74VHC244MTCX | VHC<br>244 | TSSOP20<br>(PF-Free) | 2500 Units / Tape & Reel |

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


**TSSOP20, 4.4x6.5**  
CASE 948AQ  
ISSUE A

DATE 19 MAR 2009




TOP VIEW

| SYMBOL | MIN      | NOM  | MAX  |
|--------|----------|------|------|
| A      |          |      | 1.20 |
| A1     | 0.05     |      | 0.15 |
| A2     | 0.80     |      | 1.05 |
| b      | 0.19     |      | 0.30 |
| c      | 0.09     |      | 0.20 |
| D      | 6.40     | 6.50 | 6.60 |
| E      | 6.30     | 6.40 | 6.50 |
| E1     | 4.30     | 4.40 | 4.50 |
| e      | 0.65 BSC |      |      |
| L      | 0.45     | 0.60 | 0.75 |
| L1     | 1.00 REF |      |      |
| θ      | 0°       |      | 8°   |



SIDE VIEW



END VIEW

**Notes:**

- (1) All dimensions are in millimeters. Angles in degrees.
- (2) Complies with JEDEC MO-153.

|                         |                         |                                                                                                                                                                                     |
|-------------------------|-------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>DOCUMENT NUMBER:</b> | <b>98AON34453E</b>      | Electronic versions are uncontrolled except when accessed directly from the Document Repository.<br>Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red. |
| <b>DESCRIPTION:</b>     | <b>TSSOP20, 4.4X6.5</b> | <b>PAGE 1 OF 1</b>                                                                                                                                                                  |

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)