

Metal Film Resistors, Industrial, $\pm 1\%$ Tolerance



FEATURES

- Dual power rating:
 $P_{70} = 0.25\text{ W}$ with 0.5 % stability
 $P_{70} = 0.50\text{ W}$ with 1.0 % stability
- Temperature coefficient: $\pm 100\text{ ppm/K}$
- Superior electrical performance
- Flame retardant epoxy conformal coating (red brown color)
- Standard 5 band color code marking for ease of identification after mounting
- Tape and reel packaging for automatic insertion (52.4 mm inside tape spacing per EIA-296-E)
- Lead (Pb)-free solder contacts
- Pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

STANDARD ELECTRICAL SPECIFICATIONS

PRODUCT	POWER RATING P_{70} W	LIMITING ELEMENT VOLTAGE MAX. V_{E}	TEMPERATURE COEFFICIENT $\pm\text{ ppm/K}$	TOLERANCE $\pm\%$	RESISTANCE RANGE Ω	E-SERIES
CCF55	0.25	250	100	1	10 to 3.01M	E96
CCF55	0.5	250	100	1	10 to 3.01M	E96


TECHNICAL SPECIFICATIONS

PARAMETER	UNIT	CCF55
Rated Dissipation, P_{70}	W	0.25/0.5
Maximum Working Voltage, U_{max}	V E	≤ 250
Insulation Voltage (1 min)	V eff	500
Dielectric Strength	V AC	450
Insulation Resistance	Ω	$\geq 10^{11}$
Operating Temperature Range	$^{\circ}\text{C}$	-65 to +165
Terminal Strength (pull test)	lb	2
Weight	g	0.35 max.

PART NUMBER AND PRODUCT DESCRIPTION

PART NUMBER: CCF55301RFKE36

C	C	F	5	5	3	0	1	R	F	K	E	3	6			
PRODUCT	RESISTANCE VALUE		TOLERANCE CODE		TEMPERATURE COEFFICIENT		PACKAGING				SPECIAL					
CCF55	R = Decimal K = Thousand M = Million 10R0 = 10 Ω 680K = 680 kΩ 1M00 = 1.0 MΩ		F = ± 1 %		K = 100 ppm/K		E36 = Lead (Pb)-free CCF55 = T/R (5000 pieces)				Blank = Standard (dash number) (up to 3 digits) From 1 to 999 as applicable					


DIMENSIONS in inches (millimeters)


PRODUCT	A	B	C (Max.)	D	E
CCF55	0.245 ± 0.020 (6.22 $\pm$ 0.51)	0.090 ± 0.008 (2.29 $\pm$ 0.20)	0.295 (7.5)	0.022 ± 0.002 (0.58 $\pm$ 0.05)	1.100 ± 0.040 (27.94 $\pm$ 1.02)

RESISTANCE VALUES

Vishay CCF55 is available in the standard 96 resistance values per decade. Values are obtained from the following decade table by multiplying by powers of 10. As an example: 30.1 can represent 30.1 Ω , 301 Ω , 3.01 k Ω , 30.1 k Ω or 301 k Ω .

10.0	14.7	21.5	31.6	46.4	68.1
10.2	15.0	22.1	32.4	47.5	69.8
10.5	15.4	22.6	33.2	48.7	71.5
10.7	15.8	23.2	34.0	49.9	73.2
11.0	16.2	23.7	34.8	51.1	75.0
11.3	16.5	24.3	35.7	52.3	76.8
11.5	16.9	24.9	36.5	53.6	78.7
11.8	17.4	25.5	37.4	54.9	80.6
12.1	17.8	26.1	38.3	56.2	82.5
12.4	18.2	26.7	39.2	57.6	84.5
12.7	18.7	27.4	40.2	59.0	86.6
13.0	19.1	28.0	41.2	60.4	88.7
13.3	19.6	28.7	42.2	61.9	90.9
13.7	20.0	29.4	43.2	63.4	93.1
14.0	20.5	30.1	44.2	64.9	95.3
14.3	21.0	30.9	45.3	66.5	97.6

DERATING

MARKING

The nominal resistance and tolerance are marked on the resistor using five colored bands in accordance with IEC 60062, marking codes for resistors and capacitors.

PERFORMANCE

RATED DISSIPATION, P_{70}		
CCF55	1/4 W	1/2 W
TEST ⁽¹⁾	MAXIMUM ΔR	MAXIMUM ΔR
Thermal Shock	$\pm 0.5 \%$	-
Short Time Overload	$\pm 0.5 \%$	-
Low Temperature Operation	$\pm 0.5 \%$	-
Moisture Resistance	$\pm 1.5 \%$	-
Resistance to Soldering Heat	$\pm 0.5 \%$	-
Shock/Bump	$\pm 0.5 \%$	-
Vibration	$\pm 0.5 \%$	-
Life	$\pm 0.5 \%$	$\pm 1.0 \%$
Terminal Strength	$\pm 0.2 \%$	-
Dielectric Withstanding Voltage	$\pm 0.5 \%$	-

Note

⁽¹⁾ Test specifications as per IEC 60115-1



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

CCF555100FKR36	CCF55510RFKR36	CCF5516K9FKR36	CCF5571K5FKR36	CCF55357KFHR362
CCF551K91FKR36	CCF556K19FHR362	CCF5590R9FHR362	CCF5546K4FKR36	CCF5516K5FKR36
CCF55475KFHR362	CCF558K87FHR362	CCF55115RFHR362	CCF5553K6FHR362	CCF5563K4FKR36
CCF55221RFKR36	CCF55174RFHR362	CCF5528K0FHR362	CCF55133RFHR362	CCF55130RFHR362
CCF55191RFHR362	CCF55196RFHR362	CCF55137RFHR362	CCF55169KFKR36	CCF55118RFHR362
CCF55110RFHR362	CCF5520K0FHR362	CCF55113RFHR362	CCF5554K9FKR36	CCF551M13FKR36
CCF551K13FKR36	CCF5516R9FHR362	CCF55147KFHR362	CCF552K37FKR36	CCF5580R6FKR36
CCF551K18FKR36	CCF5547K5FHR362	CCF551K54FKR36	CCF55182KFHR362	CCF5518K2FKR36
CCF55909RFKR36	CCF55187KFHR362	CCF554K99FHR362	CCF55261KFHR362	CCF55267KFHR362
CCF5541K2FHR362	CCF555K76FKR36	CCF5514R7FHR362	CCF5533R2FKR36	CCF55412KFKR36
CCF552K55FKR36	CCF55102KFHR362	CCF5584R5FKR36	CCF5536R5FKR36	CCF55205KFKR36
CCF5512R7FKR36	CCF554K53FHR362	CCF5527R4FKR36	CCF5586R6FKR36	CCF55100KFHR362
CCF5530R9FKR36	CCF55162KFHR362	CCF55576KFKR36	CCF552K15FKR36	CCF55107RFKR36
CCF55432KFHR362	CCF552M26FKR36	CCF551K58FKR36	CCF55182RFKR36	CCF55100RFKR36
CCF5533R2FHR362	CCF55105RFKR36	CCF55162RFKR36	CCF55140RFKR36	CCF55150RFKR36
CCF55464KFKR36	CCF55174RFKR36	CCF551330FKFR36	CCF5521R5FKR36	CCF55115RFKR36
CCF552M21FKR36	CCF55196RFKR36	CCF55110RFKR36	CCF5528R7FHR362	CCF55383KFHR362
CCF5575R0FKR36	CCF5545K3FHR362	CCF551K47FKR36	CCF55301KFHR362	CCF553K48FHR362
CCF5546R4FHR362	CCF5523K7FHR362	CCF552M94FKR36	CCF5523K2FHR362	CCF552M00FKR36
CCF5595R3FHR362	CCF55732KFKR36	CCF552K00FKR36	CCF55866RFKR36	CCF55976KFKR36