



260-9S & 260-9SP

Industrial Safety VOM

- Certified to EN61010-1 to 600V, Category III for safety
- Self-contained AC current measurement up to 10 Amps
- Overload protection available
- Includes test lead set with retractable banana jacks and carrying case



The new 260 Volt-Ohm-Meter is suitable for testing most commercial and industrial installations and is rated for Category III-600V applications.

Safety is the major design feature of the 260-9S/9SP and the reputation, advantages and reliability of Simpson test equipment is guaranteed.

Specifications:

DC RANGES		AC RANGES		RESISTANCE	DECIBEL
<u>Voltage</u>	<u>Current</u>	<u>Voltage</u>	<u>Current</u>	Rx1 = 0-2K Ω	-20 to +43db
0-250mV	0-1mA	0-2.5V	10A	Rx100 = 0-200K Ω	Reference: 0dB = 1mW into 600
0-2.5V	0-10mA	0-10V	Note: Up to 250 AC Amps w/Amp Clamp Accessory 150-2. See below.	Rx10K = 0-200M Ω	Ohms
0-10V	0-100mA	0-25V		Batteries: 1.5V AA, 9V (NEDA No. 13F, 1604A)	
0-25V	0-600mA	0-60V		Accuracy: Better than $\pm 2.5^\circ$ of Arc on Rx1 and $\pm 2^\circ$ of arc for Rx100 and Rx10K range. Some improvement possible by careful zero setting.	SIZE AND WEIGHT
0-60V	0-10A	0-100V		Fuse: F1 1A, 250V type 3AG, quick acting littelfuse type 312001; F2 2A, 600V littelfuse type BLS or 2A 600V, Bussman Type BBS.	Width: 5 1/4" (13.34 cm)
0-100V		0-250V			Length: 7" (17.78 cm)
0-250V		0-600V			Depth: 3 1/8" (7.94 cm)
0-600V					2 1/4 lbs. (1.02 kg)
Sensitivity: 20K Ohms Per Volt		Sensitivity: 5K Ohms Per Volt			
Insertion Loss (mV drop): 250mV		Insertion Loss (mV drop): 250mV			
Accuracy: $\pm 2\%$ of Full Scale		Accuracy: $\pm 3\%$ of Full Scale			

Ordering Information:

<u>Item</u>	<u>Part No.</u>	<u>Replacement Accessories</u>	<u>Part No.</u>	<u>Other Accessories</u>	<u>Part No.</u>
Model 260-9S Safety VOM with case	12397	Case, Nylon Padded, Safety		150-2 AC Clamp Adapter	00541
Model 260-9SP Safety VOM, protected w/case	12398	Orange, 260	00838	Clip Set, Alligator, Screw On	00425
		Test Lead Set, Retractable			
		Banana, Probe Tip	07546		