TOSHIBA Field Effect Transistor Silicon N Channel MOS Type (U-MOSIV)

## TK100F04K3

Swiching Regulator, DC-DC Converter Applications Motor Drive Applications

- AEC-Q101 qualified
- Low drain-source ON resistance: RDS (ON) =  $2.5 \text{ m}\Omega$  (typ.)
- High forward transfer admittance:  $|Y_{fs}| = 174 \text{ S (typ.)}$
- Low leakage current:  $I_{DSS} = 10 \mu A \text{ (max) (V}_{DS} = 40 \text{ V)}$
- Enhancement-model:  $V_{th} = 3.0 \text{ to } 4.0 \text{ V (V}_{DS} = 10 \text{ V, I}_{D} = 1 \text{ mA})$

#### **Absolute Maximum Ratings (Ta = 25°C)**

Characteristics			Symbol	Rating	Unit	
Drain-source voltage			$V_{DSS}$	40	V	
Drain-gate voltage ( $R_{GS} = 20 \text{ k}\Omega$ )			$V_{DGR}$	40	V	
Gate-source voltage			$V_{GSS}$	±20	→ v	
Drain current	DC	(Note 1)	I <sub>D</sub>	100	Α	
	Pulse	(Note 1)	I <sub>DP</sub>	300		
Drain power dissipation (Tc = 25°C)			P <sub>D</sub>	180	/ (w	
Single pulse avalanche energy (Note 2)			EAS	125	E	
Avalanche current			IAR	100	A	
Repetitive avalanche energy (Note 3)			EAR	18	Γm	
Channel temperature (Note 4)			Tch	175	ç	
Storage temperature range (Note 4)			T <sub>stg</sub>	-55 to 175	°C	

# 

Weight: 1.07 g (typ.)

#### **Thermal Characteristics**


Characteristics	Symbol	Max	Unit
Thermal resistance, channel to case	R <sub>th (ch-c)</sub>	0.83	°C/W

Note 1: Please use devices on condition that the channel temperature is below 175°C.

Note 2: 
$$V_{DD} = 25 \text{ V}$$
,  $T_{ch} = 25 ^{\circ}\text{C}$ ,  $L = 13 \mu\text{H}$ ,  $R_G = 25 \Omega$ ,  $I_{AR} = 100 \text{ A}$ 

Note 3: Repetitive rating; pulse width limited by maximum channel temperature.

Note 4: 175°C refers to AEC-Q101.



Please design the appropriate reliability upon reviewing the Toshiba Semiconductor Reliability Handbook ("Handling Precautions"/"Derating Concept and Methods") and individual reliability data (i.e. reliability test report and estimated failure rate, etc).

This transistor is an electrostatic sensitive device. Please handle with caution


Start of commercial production 2008-03

#### **Electrical Characteristics (Ta = 25°C)**

Characteristics		Symbol	Test Condition	Min	Тур.	Max	Unit	
Gate leakage cur	rent	I <sub>GSS</sub>	$V_{GS} = \pm 20 \text{ V}, V_{DS} = 0 \text{ V}$	_	_	±10	μΑ	
Drain cut-OFF cu	rrent	I <sub>DSS</sub>	V <sub>DS</sub> = 40 V, V <sub>GS</sub> = 0 V	_	_	10	μА	
Drain-source breakdown voltage		V (BR) DSS	$I_D = 10 \text{ mA}, V_{GS} = 0 \text{ V}$	40	_	_	٧	
		V (BR) DSX	$I_D = 10 \text{ mA}, V_{GS} = -20 \text{ V}$	20	/	_		
Gate threshold vo	oltage	V <sub>th</sub>	V <sub>DS</sub> = 10 V, I <sub>D</sub> = 1 mA	3.0	))_	4.0	٧	
Drain-source ON resistance		R <sub>DS</sub> (ON)	V <sub>GS</sub> = 10 V, I <sub>D</sub> = 50 A	7	2.5	3.0	mΩ	
Forward transfer admittance		Y <sub>fs</sub>	V <sub>DS</sub> = 10 V, I <sub>D</sub> = 50 A	87	174	_	S	
Input capacitance	e	C <sub>iss</sub>		> —	4500	_		
Reverse transfer capacitance		C <sub>rss</sub>	$V_{DS} = 10V, V_{GS} = 0 V, f = 1 MHz$	_	900	_	pF	
Output capacitance		C <sub>oss</sub>			1100	/		
Switching time Fa	Rise time	t <sub>r</sub>	, 10 V ☐ ()b € 50 A	-6	21	> —	ns	
	Turn-ON time	t <sub>on</sub>	$V_{GS}$ $0 V$ $R_L = 0.4 \Omega$		37	_		
	Fall time	t <sub>f</sub>	V <sub>DD</sub> ≈ 20 V		31	_		
	Turn-OFF time	t <sub>off</sub>	Duty ≤ 1%, t <sub>w</sub> = 10 μs	) —	75	_		
Total gate charge (gate-source plus gate-drain)		Qg		_	102	_	_	
Gate-source charge		Qgs	$V_{DD} \approx 32 \text{ V}, V_{GS} = 10 \text{ V}, I_{D} = 100 \text{ A}$	_	56		nC	
Gate-drain ("miller") charge		Q <sub>gd</sub>		_	46	_		

### Source-Drain Ratings and Characteristics (Ta = 25°C

Characteristics	Symbol	Test Condition	Min	Тур.	Max	Unit
Continuous drain reverse current (Note 1)	I <sub>DR</sub>	_	_	_	100	Α
Pulse drain reverse current (Note 1)	IDRR		_	_	300	Α
Forward voltage (diode)	V <sub>DSF</sub>	$I_{DR} = 100 \text{ A}, V_{GS} = 0 \text{ V}$	_	_	-1.2	V
Reverse recovery time	/\\$rr	$I_{DR} = 100 \text{ A}, V_{GS} = 0 \text{ V},$	_	61	_	ns
Reverse recovery charge	Qrr	dI <sub>DR</sub> /dt = 50 A/μs		49	_	nC



Note 6: A line under a Lot No. identifies the indication of product Labels. [[G]]/RoHS COMPATIBLE or [[G]]/RoHS [[Pb]]

Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product. The RoHS is the Directive 2011/65/EU of the European Parliament and of the Council of 8 June 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment.

2 2014-09-26



Moisture-Proof Packing

The TK100F04K3 is packed in a moisture-proof laminated aluminum bag.

Precautions for Transportation and Storage

- (1) Avoid excessive vibration during transportation.
- (2) Do not toss or drop the packed devices to avoid ripping of the bag.
- (3) After opening the moisture-proof bag, the devices should be assembled within two weeks in an environment of 5°C to 30°C and RH70% or below. Perform reflow at most twice.
- (4) The moisture-proof bag may be stored unopened for up to 12 months at 5°C to 30°C and RH90% or below.
- (5) If, upon opening the bag, the moisture indicator card shows humidity of 30% or above (the color of the 30% dot has changed from blue to pink) or the expiration date has passed, the devices should be baked as follows:


  Baking conditions: 125°C for 48 hours.

Since the tape materials are not heat-proof, devices should be placed on either heat-proof trays or aluminum magazines when baking.




The humidity indicator shows an approximate ambient humidity at 25°C. If the ambient humidity is below 30%, the color of all the indicator dots is blue. If, upon opening the bag, the color of the 30% dot has changed from blue to pink, the devices should be baked before assembly.


3 2014-09-26



4



5



#### **RESTRICTIONS ON PRODUCT USE**

- Toshiba Corporation, and its subsidiaries and affiliates (collectively "TOSHIBA"), reserve the right to make changes to the information in this document, and related hardware, software and systems (collectively "Product") without notice.
- This document and any information herein may not be reproduced without prior written permission from TOSHIBA. Even with TOSHIBA's written permission, reproduction is permissible only if reproduction is without alteration/omission.
- Though TOSHIBA works continually to improve Product's quality and reliability, Product can malfunction or fail. Customers are responsible for complying with safety standards and for providing adequate designs and safeguards for their hardware, software and systems which minimize risk and avoid situations in which a malfunction or failure of Product could cause loss of human life, bodily injury or damage to property, including data loss or corruption. Before customers use the Product, create designs including the Product, or incorporate the Product into their own applications, customers must also refer to and comply with (a) the latest versions of all relevant TOSHIBA information, including without limitation, this document, the specifications, the data sheets and application notes for Product and the precautions and conditions set forth in the "TOSHIBA Semiconductor Reliability Handbook" and (b) the instructions for the application with which the Product will be used with or for. Customers are solely responsible for all aspects of their own product design or applications, including but not limited to (a) determining the appropriateness of the use of this Product in such design or applications; (b) evaluating and determining the applicability of any information contained in this document, or in charts, diagrams, programs, algorithms, sample application circuits, or any other referenced documents; and (c) validating all operating parameters for such designs and applications. TOSHIBA ASSUMES NO LIABILITY FOR CUSTOMERS' PRODUCT DESIGN OR APPLICATIONS.
- PRODUCT IS NEITHER INTENDED NOR WARRANTED FOR USE IN EQUIPMENTS OR SYSTEMS THAT REQUIRE
  EXTRAORDINARILY HIGH LEVELS OF QUALITY AND/OR RELIABILITY, AND/OR A MALFUNCTION OR FAILURE OF WHICH
  MAY CAUSE LOSS OF HUMAN LIFE, BODILY INJURY, SERIOUS PROPERTY DAMAGE AND/OR SERIOUS PUBLIC IMPACT
  ("UNINTENDED USE"). Except for specific applications as expressly stated in this document, Unintended Use includes, without
  limitation, equipment used in nuclear facilities, equipment used in the aerospace industry, medical equipment, equipment used for
  automobiles, trains, ships and other transportation, traffic signaling equipment, equipment used to control combustions or explosions,
  safety devices, elevators and escalators, devices related to electric power, and equipment used in finance-related fields. IF YOU USE
  PRODUCT FOR UNINTENDED USE, TOSHIBA ASSUMES NO LIABILITY FOR PRODUCT. For details, please contact your
  TOSHIBA sales representative.
- . Do not disassemble, analyze, reverse-engineer, alter, modify, translate or copy Product, whether in whole or in part.
- Product shall not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any
  applicable laws or regulations.
- The information contained herein is presented only as guidance for Product use. No responsibility is assumed by TOSHIBA for any infringement of patents or any other intellectual property rights of third parties that may result from the use of Product. No license to any intellectual property right is granted by this document, whether express or implied, by estoppel or otherwise.
- ABSENT A WRITTEN SIGNED AGREEMENT, EXCEPT AS PROVIDED IN THE RELEVANT TERMS AND CONDITIONS OF SALE
  FOR PRODUCT, AND TO THE MAXIMUM EXTENT ALLOWABLE BY LAW, TOSHIBA (1) ASSUMES NO LIABILITY
  WHATSOEVER, INCLUDING WITHOUT LIMITATION, INDIRECT, CONSEQUENTIAL, SPECIAL, OR INCIDENTAL DAMAGES OR
  LOSS, INCLUDING WITHOUT LIMITATION, LOSS OF PROFITS, LOSS OF OPPORTUNITIES, BUSINESS INTERRUPTION AND
  LOSS OF DATA, AND (2) DISCLAIMS ANY AND ALL EXPRESS OR IMPLIED WARRANTIES AND CONDITIONS RELATED TO
  SALE, USE OF PRODUCT, OR INFORMATION, INCLUDING WARRANTIES OR CONDITIONS OF MERCHANTABILITY, FITNESS
  FOR A PARTICULAR PURPOSE, ACCURACY OF INFORMATION, OR NONINFRINGEMENT.
- Do not use or otherwise make available Product or related software or technology for any military purposes, including without
  limitation, for the design, development, use, stockpiling or manufacturing of nuclear, chemical, or biological weapons or missile
  technology products (mass destruction weapons). Product and related software and technology may be controlled under the
  applicable export laws and regulations including, without limitation, the Japanese Foreign Exchange and Foreign Trade Law and the
  U.S. Export Administration Regulations. Export and re-export of Product or related software or technology are strictly prohibited
  except in compliance with all applicable export laws and regulations.
- Please contact your TOSHIBA sales representative for details as to environmental matters such as the RoHS compatibility of Product.
   Please use Product in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. TOSHIBA ASSUMES NO LIABILITY FOR DAMAGES OR LOSSES
   OCCURRING AS A RESULT OF NONCOMPLIANCE WITH APPLICABLE LAWS AND REGULATIONS.