

PRODUCT NUMBER


71600-YXXLF

LEAD FREE, SEE NOTE 6

TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2


OPTIONAL STRAIN RELIEF
SEE SHEET 2

TRIANGLE INDICATES
POSITION 1
NOTE 5



NOTES:

- 1 - PLASTIC MAT'L : GLASS FILLED HIGH TEMPERATURE THERMOPLASTIC. UL94V-0 COLOR: GREY
- 2 - PIN MATERIAL : PHOSPHOR BRONZE
- 3 - PRODUCT PACKAGED IN TUBES.
- 4 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS $N \times 2.54 = 20.32\text{mm}$
- 5 - 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.
- 2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO LEFT AND RIGHT POLARIZING SLOT.
- 2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT POLARIZING SLOT.
- 2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT
- 2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT
- 6 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS PER GS-22-008.
PACKAGING SPECIFICATION AS PER GS-14-920.







mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family 2.54MM IDC			
ltr	ecn no	dr	date	tolerances unless otherwise specified		X.X ±0.3				title QUICKIE III FEM			
AP	F12-0046	LMU	12.04.25	angles	linear	X.XX ±0.13				0.76µm Au			
AR	B-17851	LMU	14.06.05			X.XXX ±0.05				scale 5:1			
AK	F05-0180	LMU	05.04.22	dr	D.LE	01.01.24		dwg no		sheet 1 of 2		size	
AL	F06-0270	LMU	06.09.12	engr	P.NZ	01.01.24		71600		A			
AM	F06-0274	LMU	06.09.25	chr	JF.N	01.01.24							
AN	F09-0233	LMU	09.12.15	appd	P.NZ	01.01.24		type		CUSTOMER Drawing			
sheet index	revision sheet	AR	AF	1	2								




Copyright FCI

STRAIN RELIEF OPTION AVAILABILITY	Nbr OF POSITIONS
1/6	04
0/1/2/3/6	06
0/1/2/3/6	08
0/1/2/3/6	10
0/1/2/3/6	14
0/1/2/3/6	16
0/1/2/3/6	18
0/1/2/3/6	20
0/1/3	24
0/1/2/3/6	26
0/1/2/3/6	30
0/1/2/3/6	34
0/1/2/3/6	40
0/1/2/3/6	50
0/1/2/3/6	60
0/1/2/3/6	64
PLATING 0.76µm GOLD ON CONTACT AREA 1.27 µm Ni REMAINDER OF PRODUCT	


624
304
204 / 224
004
DASHES NOT AVAILABLE

LOW PROFILE
STRAIN RELIEFSTANDARD
STRAIN RELIEFLATCHING STRAIN RELIEF
FOR SLIM HEADER


WITHOUT STRAIN RELIEF



WITH LOW PROFILE STRAIN RELIEF



WITH STANDARD STRAIN RELIEF



WITH LATCHING STRAIN RELIEF

71600-6YYLF	●					●
71600-3YYLF		●	●			
71600-2YYLF	●				●	
71600-1YYLF	●				●	
71600-0YYLF	●		●			
PRODUCT NUMBER	WITH	WITHOUT	STANDARD	WITHOUT	LOW PROFILE	LATCHING
	CENTRAL KEY		STRAIN RELIEF			

mat'l. code				surface	tolerance	projection	product family
ltr	ecn no	dr	date	ISO 1302	ISO 406 ISO 1101	ISO 1101	QUICKIE
AF	B-17851	LMU	14.06.05	angles	linear	mm	title
AA	F10199	GCO	01.04.26			scale N/A	71600
AB	F03019	DLE	03.01.23	dr	D.LE	01.01.24	sheet 2 of - size
AC	F05-0180	LMU	05.04.22	engr	P.NZ	01.01.24	A3
AD	F06-0270	LMU	06.09.12	chr	JF.N	01.01.24	type
AE	F06-0274	LMU	06.09.25	app	P.NZ	01.01.24	CUSTOMER Drawing
sheet	revision						
index	sheet						