




- 1 CONTINUOUS STRIP ON REEL.
- 2 P/N 61760-2 IS REVERSE REELED.
- 3 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

SECTION A-A
SCALE 10:1

SECTION B-B
SCALE 10:1

3 OBSOLETE	3.56 [.140] MAX DIA	20-16 AWG	2 61760-2 61760-1
	INSULATION RANGE	WIRE RANGE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PHILLIP M. FORTNEY 05OCT98	AMP AMP Incorporated Harrisburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK JEFF R. RUTH 05OCT98		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD DONALD DECKER 05OCT98	NAME	
0 PLC ±-		PRODUCT SPEC	TERMINAL, LAMP GROUNDING	
1 PLC ±-		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
2 PLC ±0.25 [.010]			A2 00779 C- 61760	
3 PLC ±-			SCALE 6:1 SHEET 1 OF 1 REV E1	
4 PLC ±-				
ANGLES ±-				
FINISH 0.003302 [.000130]		WEIGHT -		
MAX PRE-TIN PLATE				
MATERIAL #4HD PHOS BRONZE		CUSTOMER DRAWING		